

Product data sheet

Specifications



electromechanical timing relay - 0..15 h - 127..230 V AC - 2 C/O

RE88256512

⚠ Discontinued on: Jul 1, 2020

⚠ Discontinued

Main

Range Of Product	Zelio Time
Product Or Component Type	Electromechanical timing relay
Discrete Output Type	Relay
Contacts Type And Composition	timed contact
Component Name	RE88256
Time Delay Range	0...15 h
[Us] Rated Supply Voltage	127...230 V AC 50 Hz
Electrical Connection	Cable Tag connector

Complementary

Control Type	Manual reset front panel
Voltage Range	0.85...1.1 Un 131 °F (55 °C) IEC 60255-100
Setting Accuracy Of Time Delay	+/- 4 % of full scale 0...15 h
On-Load Factor	100 %
Power Consumption In Va	3.1 VA 0.8
[Ui] Rated Insulation Voltage	380 V AC VDE 0110 group C 440 V DC VDE 0110 group C
[Ith] Conventional Free Air Thermal Current	20 A
Breaking Capacity	16 A 230 V 0.41 10000 cycles
Mechanical Durability	10000000 cycles
Fixing Mode	Screw-on panel
Net Weight	0.54 lb(US) (0.245 kg)

Environment

Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)
Ambient Air Temperature For Operation	23...158 °F (-5...70 °C)
Ip Degree Of Protection	IP10 terminal block)
Vibration Resistance	4 gn 10...55 Hz)
Dielectric Test Voltage	2 kV IEC 60255-5 2 kV VDE 0435

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Gtin	3389110281156
------	---------------

Contractual warranty

Warranty	18 months
----------	-----------