

# Product data sheet

## Characteristics

# RGF36100U74AE1

## MOLDED CASE CIRCUIT BREAKER 600V 1000A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 35,087.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact R
Current sensor rating range	1000 A
Trip unit technology	Electronic harmonic Micrologic 6.0 H LSIG

### Complementary

[Ie] rated operational current	1000 A
System Voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Breaking capacity code	G
Continuous current rating	80 %
Electrical connection	Busbar connection load Busbar connection line
Height	16.24 in
Width	16.53 in
Depth	14.49 in
Communication interface	Modbus

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

## Ordering and shipping details

Category	01245 - RG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	52
Returnability	Y
Country of origin	US

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------