

# Product data sheet

Specifications



## plug-in relay - Harmony RHN - instantaneous - 4 C/O - 24 V DC - 5 A

RHN412B

! Discontinued

! Discontinued on: Oct 11, 2021

! End-of-service on: Dec 31, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range Of Product	Harmony Relay
Product Or Component Type	Plug-in relay
Device Short Name	RHN
Contacts Type And Composition	4 C/O
Contact Operation	Instantaneous Standard
[Uc] Control Circuit Voltage	24 V DC
[Ithe] Conventional Enclosed Thermal Current	5 A 104 °F (40 °C)
Status Led	Without
Control Type	Manual control
Coil Interference Suppression	Without

### Complementary

[Ui] Rated Insulation Voltage	250 V
Test Levels	Level A group mounting
Operating Position	Any position
Minimum Switching Capacity	150 mVA 10 mA 150 mVA, 1 V
Contact Bounce Time	<= 10 ms
Maximum Voltage Drop	<100 V for 3 A at 24 V
Average Resistance	30 mOhm 68 °F (20 °C)
Average Coil Consumption	1.6 W 68 °F (20 °C)
Control Circuit Voltage Limits	0.8...1.1 Uc IEC 60255
Drop-Out Voltage Threshold	0.1...0.3 Uc
Time Constant	12 ms open 15 ms closed
Mechanical Durability	20000000 cycles
Maximum Operating Rate	6 cyc/mn

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Time	1...4 ms energisation/de-energisation 1.2...4 ms de-energisation/energisation 10...20 ms between energisation of coil and closing of NO contact 68 °F (20 °C) 2...7 ms between de-energisation of coil and closing of NC contact 68 °F (20 °C)
Cad Overall Width	1.30 in (33 mm)
Cad Overall Height	1.69 in (43 mm)
Cad Overall Depth	2.13 in (54 mm)
Terminals Description Iso N°1	(11-12-14)OC (21-22-24)OC (41-42-44)OC (31-32-34)OC (A1-A2)CO
Net Weight	0.20 lb(US) (0.09 kg)
Compatibility Code	RHN

## Environment

Standards	NF C 45-250 VDE 0435 IEC 60255 BS 4794
Product Certifications	USSR BV CSA EDF ASE UR
Protective Treatment	TC
Dielectric Strength	2500 V
Ambient Air Temperature For Operation	23...104 °F (-5...40 °C) IEC 60255
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	6 gn 10...55 Hz)IEC 60068-2-6 6 gn 10...55 Hz)NF C 20-616
Shock Resistance	50 gn 11 ms NF C 20-608

## Ordering and shipping details

Category	US10CP218073
Discount Schedule	0CP2
Gtin	3389110162905
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.05 in (5.2 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	3.07 in (7.8 cm)
Package 1 Weight	3.32 oz (94 g)

# Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>