





Circuit breaker, PowerPacT R, 2000A, 3 pole, 600VAC, 65kA, busbar, Micrologic 5.0, 80%

RKF36200U33A

! Discontinued on: Nov 20, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	PowerPact	
Product Name	PowerPact R	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Line Rated Current	2000 A	
Number Of Poles	3P	
Control Type	Operating handle	
Breaking Capacity Code	К	
Breaking Capacity	AIR 65 kA 240 V AC 50/60 Hz UL 489 AIR 65 kA 480 V AC 50/60 Hz UL 489 AIR 65 kA 600 V AC 50/60 Hz UL 489 Icu 85 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 70 kA 380/415 V AC 50/60 Hz IEC 60947-2	
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489	
Network Frequency	50/60 Hz	
[Ics] Rated Service Breaking Capacity	65 kA 240 V AC 50/60 Hz IEC 60947-2 55 kA 380/415 V AC 50/60 Hz IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2	
Trip Unit Technology	Electronic, standard, MicroLogic 5.0, LSI	
Continuous Current Rating	80 %	
[Ui] Rated Insulation Voltage	750 V IEC 60947-2	
Trip Unit Name	MicroLogic 5.0	
Suitability For Isolation	Yes IEC 60947-2	
Utilisation Category	Category A	
Awg Gauge	AWG 3/0750 kcmil aluminium/copper	
Local Signalling	Alarm 1 LED yellow)long-time pick up)	
Mounting Mode	Unit mount busbar)	
Mounting Support	Busbar	
Electrical Connection	Busbar connection, line Busbar connection, load	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Terminal Identifier	AL2500RK	
Tightening Torque	601.85 lbf.in (68 N.m) 0.080.62 in² (50400 mm²) (AWG 1/0750 kcmil) 601.85 lbf.in (68 N.m) 0.080.23 in² (50150 mm²) (2 x AWG 1/02 x 300 kcmil)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	1.38 in (35 mm)	
Height	16.24 in (412.50 mm)	
Width	16.54 in (420.12 mm)	
Depth	14.49 in (368.05 mm)	
Net Weight	52 lb(US) (23.59 kg)	
Quantity Per Set	1	
Circuit Breaker Application	HACR rated	

### **Environment**

Quality Labels	CE
Standards	UL CSA NEMA NMX J-266 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating

# Ordering and shipping details

Category	US10DE201245	
Discount Schedule	0DE2	
Gtin	3606486286722	
Returnability	Yes	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	16.22 in (41.2 cm)	
Package 1 Width	16.54 in (42.0 cm)	
Package 1 Length	14.49 in (36.8 cm)	
Package 1 Weight	74.00 lb(US) (33.566 kg)	

## **Contractual warranty**

Warranty

18 months

# Sustainability Green Premium\*

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov