Specifications



# Circuit breaker, PowerPacT R, 1600A, 3 pole, 600VAC, 50kA, busbar, Micrologic 5.0H, 100%, modbus

RLF36160CU73AE1

#### Main

Range	PowerPact	
Product Name	PowerPact R	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Complementary	
Line Rated Current	1600 A
Number Of Poles	3P
Control Type	Operating handle
Breaking Capacity Code	L
Breaking Capacity	AIR 125 kA 240 V AC 50/60 Hz UL 489 AIR 100 kA 480 V AC 50/60 Hz UL 489 AIR 50 kA 600 V AC 50/60 Hz UL 489 Icu 125 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 85 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA 240 V AC 50/60 Hz IEC 60947-2 45 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, harmonic, MicroLogic 5.0 H, LSI
Continuous Current Rating	100 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 5.0 H
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 3/0750 kcmil aluminium/copper
Local Signalling	Alarm 1 LED yellow)long-time pick up) 1 LED red)long-time pick up) Trip causes 1 LED red) 1 LED red)digital ammeter) Phase-loading LED green)load balancing)
Mounting Mode	Unit mount busbar)
Mounting Support	Busbar
Electrical Connection	Busbar connection, line Busbar connection, load

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Terminal Identifier	AL2500RK	
Tightening Torque	548.75 lbf.in (62 N.m) 0.080.62 in² (50400 mm²) (AWG 1/0750 kcmil) 548.75 lbf.in (62 N.m) 0.080.23 in² (50150 mm²) (2 x AWG 1/02 x 300 kcmil)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	1.38 in (35 mm)	
Height	16.24 in (412.50 mm)	
Width	16.54 in (420.12 mm)	
Depth	14.49 in (368.05 mm)	
Net Weight	52 lb(US) (23.59 kg)	
Quantity Per Set	1	
Communication Interface	Modbus	
Circuit Breaker Application	HACR rated	

### Environment

Quality Labels	CE	
Standards	UL CSA NEMA NMX J-266 IEC 60947-2	
Product Certifications	UL CSA NOM	
Ip Degree Of Protection	IP40	
Pollution Degree	3 IEC 60947-1	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating	

# Ordering and shipping details

Category	01245-RG,H,J,K,L,N UNIT MT BREAKERS	
Discount Schedule	DE2	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.22 in (41.2 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	14.49 in (36.8 cm)
Package 1 Weight	52.00 lb(US) (23.587 kg)

# **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov