Specification





level control relay, Harmony Control Relays, 8A, 1CO, 24…240V AC DC

RM22LG11MR

Product availability: Stock - Normally stocked in distribution

acility

Price*: 52.45 USD

Main

Range Of Product	Harmony Control Relays
Relay Type	Level control relay
Product Or Component Type	Level control relay
Relay Name	RM22L
Relay Monitored Parameters	Detection by resistive probes
Time Delay	Without
Switching Capacity In Va	2000 VA
Minimum Switching Current	10 mA 5 V DC
Maximum Switching Current	8 A AC
Utilisation Category	AC-15 IEC 60947-5-1 DC-13 IEC 60947-5-1 AC-1 IEC 60947-4-1 DC-1 IEC 60947-4-1
Contacts Type And Composition	2 C/O

Complementary

Maximum Switching Voltage	250 V AC
[Un] Rated Nominal Voltage	24240 V AC/DC 50/60 Hz, non self-powered
Supply Voltage Limits	20.4264 V AC/DC
Power Consumption	1.5 W DC
Output Contacts	2 C/O
Nominal Output Current	8 A
Delay At Power Up	0.6 s
Maximum Electrode Voltage	12 V AC
Maximum Electrode Current	1 mA
Repeat Accuracy	+/- 2 % time delay
Measurement Error	< 1 % over the whole range with voltage variation 0.05 %/°C with temperature variation
Maximum Cable Distance Between Devices	3280.84 ft (1000 m) probe and delay
Sensitivity Scale	5100 kOhm St (Standard Sensitivity)
Sensitivity Adjustment	5100 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Supply Current For Sensors	1 mA
Cable Capacitance	1 nF HS (High Sensitivity) probe cable 2.2 nF St (Standard Sensitivity) probe cable 4.7 nF LS (Low Sensitivity) probe cable
Overvoltage Category	III IEC 60664-1
Insulation	Between supply and measurement
Connections - Terminals	Screw terminals, 2 x 0.52 x 2.5 mm² AWG 20AWG 14) solid without cable end Screw terminals, 2 x 0.22 x 1.5 mm² AWG 24AWG 16) flexible with cable end Screw terminals, 1 x 0.51 x 3.3 mm² AWG 20AWG 12) solid without cable end Screw terminals, 1 x 0.21 x 2.5 mm² AWG 24AWG 14) flexible with cable end
Tightening Torque	5.318.85 lbf.in (0.61 N.m) IEC 60947-1
Housing Material	Self-extinguishing plastic
Mounting Support	35 mm DIN rail conforming to IEC 60715
Mounting Position	Any position
Electrical Durability	100000 cycles
Mechanical Durability	10000000 cycles
Contacts Material	Cadmium free
Measurement Range	5100 kOhm
Safety Reliability Data	B10d = 120000 MTTFd = 125.5 years
Width	0.89 in (22.5 mm)
Control Type	With test button
Net Weight	0.22 lb(US) (0.1 kg)
Environment	
Immunity To Microbreaks	100 ms DC 90 ms AC
Electromagnetic Compatibility	Immunity for residential, commercial and light-industrial environments conforming to IEC 61000-6-1 Immunity for industrial environments conforming to IEC 61000-6-2 Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3
	Emission standard for industrial environments conforming to IEC 61000-6-4 Electrostatic discharge - test level: 6 kV level 3 (contact discharge) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV level 3 (air discharge) conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test - test level: 10 V/m level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test - test level: 4 kV level 4 (direct) conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test - test level: 2 kV level 4 (capacitive coupling) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV level 4 (common mode) conforming to IEC 61000-4-5 Surge immunity test - test level: 2 kV level 4 (differential mode) conforming to IEC 61000-4-5 Conducted and radiated emissions class B group 1 conforming to CISPR 11 Conducted and radiated emissions class B conforming to CISPR 22

GL RCM CCC CSA UL EAC

CE

Product Certifications

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Relative Humidity	9397 % 77131 °F (2555 °C) IEC 60068-2-30
Vibration Resistance	0.075 mm 1058.1 Hz) not in operation IEC 60068-2-6 1 gn 1058.1 Hz) not in operation IEC 60068-2-6 0.035 mm 58.1150 Hz) in operation IEC 60068-2-6 0.5 gn 58.1150 Hz) in operation IEC 60068-2-6
Shock Resistance	15 gn 11 ms) not in operation IEC 60068-2-27 5 gn 11 ms) in operation IEC 60068-2-27
Ip Degree Of Protection	IP20 IEC 60529 terminals) IP40 IEC 60529 housing) IP50 IEC 60529 front panel)
Pollution Degree	3 IEC 60664-1
Dielectric Test Voltage	2.5 kV AC 50 Hz, 1 min IEC 60255-27

Ordering and shipping details

Category	US10CP222380
Discount Schedule	0CP2
Gtin	3606480792328
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.02 in (2.6 cm)
Package 1 Width	3.23 in (8.2 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	3.84 oz (109.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.02 lb(US) (4.999 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	640
Package 3 Height	29.53 in (75.0 cm)
Package 3 Width	23.62 in (60.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	195.07 lb(US) (88.484 kg)

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·


Apr 25, 2024

RM22LG11MR

Dimensions Drawings

Dimensions






RM22LG11MR

Mounting and Clearance

Mounting and Clearance

Rail Mounting




RM22LG11MR

Connections and Schema

Level Control Relay

Wiring Diagram




A1,A2 : Supply voltage
Max : High level
Min : Low level

C: References or Tank earth electrode 11-14,12: 1st C/O contact of output relay

Control by Electrodes

Wiring Diagram



A1,A2 : Supply voltage Max : High level Min : Low level


C: References or Tank earth electrode 11-14,12: 1st C/O contact of output relay

Technical Description

Function Diagrams

Control of Two Levels

Fill/Empty function



Legend

Un Nominal supply voltage


(1) Min. level(2) Max. level

11-12/11-14, 21-22/21-24 Output relay connections


Relay status: black color = energized.

Control of One Level


Empty function T on



Empty function T off




Fill function T on



Fill function T off

RM22LG11MR



Legend

10

Tt Time delay after crossing of threshold **Un** Supply voltage

(1) Level threshold

11-12/11-14, 21-22/21-24 Output relay connections

Relay status: black color = energized.