Specifications





plug-in relay, Harmony electromechanical relays, 15A, 3CO, with LED, lockable test button, 48V DC

RPM32ED

① Discontinued

() Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Power
Product Or Component Type	Plug-in relay
Device Short Name	RPM
Contacts Type And Composition	3 C/O
[Uc] Control Circuit Voltage	48 V DC
[Ithe] Conventional Enclosed Thermal Current	15 A -40131 °F (-4055 °C)
Status Led	With
Control Type	Lockable test button
Utilisation Coefficient	20 %

Complementary

Shape Of Pin	Flat
[Ui] Rated Insulation Voltage	250 V IEC
	300 V CSA
	300 V UL
[Uimp] Rated Impulse Withstand Voltage	4 kV 1.2/50 μs
Contacts Material	AgNi
[le] Rated Operational Current	15 A 277 V AC) UL
	15 A 28 V DC) UL
	15 A 250 V AC) NO IEC
	15 A 28 V DC) NO IEC
	7.5 A 250 V AC) NC IEC
	7.5 A 28 V DC) NC IEC
Maximum Switching Voltage	250 V IEC
Resistive Load Current	15 A 250 V AC
	15 A 28 V DC
Maximum Switching Capacity	3750 VA
	420 W
Minimum Switching Capacity	170 mW 10 mA, 17 V
Operating Rate	<= 1200 cycles/hour under load
	<= 18000 cycles/hour no-load
Mechanical Durability	1000000 cycles

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Durability	100000 cycles resistive
Average Coil Consumption	1.5 W
Drop-Out Voltage Threshold	>= 0.1 Uc DC
Operate Time	20 ms at nominal voltage
Release Time	20 ms at nominal voltage
Average Coil Resistance	1280 Ohm at 68 °F (20 °C) +/- 10 %
Rated Operational Voltage Limits	38.452.8 V DC
Protection Category	RTI
Test Levels	Level A group mounting
Operating Position	Any position
Pollution Degree	3
Safety Reliability Data	B10d = 100000
Net Weight	0.12 lb(US) (0.054 kg)
Device Presentation	Complete product

Environment

Dielectric Strength	1500 V AC between contacts with micro disconnection 2000 V AC between coil and contact with reinforced 2000 V AC between poles with basic
Standards	CSA C22.2 No 14 EN/IEC 61810-1 UL 508
Product Certifications	CSA UL EAC
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)
Vibration Resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating
Degree Of Protection (Housing Only)	IP40 conforming to EN/IEC 60529
Shock Resistance	15 gnin operation 30 gnnot operating

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
Gtin	3389119402071
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.30 in (3.3 cm)

Package 1 Length1.97 in (5 cm)Package 1 Weight1.94 oz (55 g)Unit Type Of Package 2BB1Number Of Units In Package 210Package 2 Height1.22 in (3.1 cm)Package 2 Width4.13 in (10.5 cm)Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 380Package 3 Height5.91 in (15 cm)Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length10.34 lb(US) (4.689 kg)		
Unit Type Of Package 2BB1Number Of Units In Package 210Package 2 Height1.22 in (3.1 cm)Package 2 Width4.13 in (10.5 cm)Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Package 1 Length	1.97 in (5 cm)
Number Of Units In Package 210Package 2 Height1.22 in (3.1 cm)Package 2 Width4.13 in (10.5 cm)Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Package 1 Weight	1.94 oz (55 g)
Package 2 Height1.22 in (3.1 cm)Package 2 Width4.13 in (10.5 cm)Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Unit Type Of Package 2	BB1
Package 2 Width4.13 in (10.5 cm)Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Number Of Units In Package 2	10
Package 2 Length6.93 in (17.6 cm)Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Package 2 Height	1.22 in (3.1 cm)
Package 2 Weight19.68 oz (558 g)Unit Type Of Package 3S01Number Of Units In Package 380Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Package 2 Width	4.13 in (10.5 cm)
Unit Type Of Package 3 S01 Number Of Units In Package 3 80 Package 3 Height 5.91 in (15 cm) Package 3 Width 5.91 in (15 cm) Package 3 Length 15.75 in (40 cm)	Package 2 Length	6.93 in (17.6 cm)
Number Of Units In Package 3 80 Package 3 Height 5.91 in (15 cm) Package 3 Width 5.91 in (15 cm) Package 3 Length 15.75 in (40 cm)	Package 2 Weight	19.68 oz (558 g)
Package 3 Height5.91 in (15 cm)Package 3 Width5.91 in (15 cm)Package 3 Length15.75 in (40 cm)	Unit Type Of Package 3	S01
Package 3 Width 5.91 in (15 cm) Package 3 Length 15.75 in (40 cm)	Number Of Units In Package 3	80
Package 3 Length 15.75 in (40 cm)	Package 3 Height	5.91 in (15 cm)
	Package 3 Width	5.91 in (15 cm)
Package 3 Weight 10.34 lb(US) (4.689 kg)	Package 3 Length	15.75 in (40 cm)
	Package 3 Weight	10.34 lb(US) (4.689 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Dimensions

mm in.






Pin Side View



Connections and Schema

Wiring Diagram




Symbols shown in blue correspond to Nema marking.

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.