Specifications





universal plug-in relay - Harmony RUM - 2 C/O - 110 V DC - 10 A with LED

RUMC23FD

() Discontinued on: Jan 23, 2021

① Discontinued

Main

Range Of Product	Harmony Relay
Series Name	Universal
Product Or Component Type	Plug-in relay
Device Short Name	RUM
Contacts Type And Composition	2 C/O
[Uc] Control Circuit Voltage	110 V DC
[Ithe] Conventional Enclosed Thermal Current	10 A -40131 °F (-4055 °C)
Status Led	With
Control Type	Without lockable test button
Utilisation Coefficient	20 %

Complementary

Shape Of Pin	Cylindrical
[Ui] Rated Insulation Voltage	250 V IEC
	300 V CSA
	300 V UL
[Uimp] Rated Impulse Withstand Voltage	4 kV 1.2/50 μs)
Contacts Material	AgNi
[le] Rated Operational Current	10 A at 277 V AC conforming to UL
	10 A at 30 V DC conforming to UL
	10 A at 30 V DC conforming to CSA
	5 A at 250 V AC (NC) conforming to IEC
	5 A at 28 V DC (NC) conforming to IEC
	10 A at 250 V AC (NO) conforming to IEC
	10 A at 28 V DC (NO) conforming to IEC
	10 A at 277 V AC conforming to CSA
Maximum Switching Voltage	250 V IEC
Resistive Rated Load	10 A 250 V AC
	10 A 28 V DC
Maximum Switching Capacity	2500 VA/280 W
Minimum Switching Capacity	170 mW 10 mA, 17 V
Operating Rate	<= 18000 cycles/hour no-load
	<= 1200 cycles/hour under load
Mechanical Durability	5000000 cycles
Electrical Durability	100000 cycles resistive

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Average Coil Consumption In W	1.4 W	
Drop-Out Voltage Threshold	>= 0.1 Uc DC	
Operate Time	20 ms at nominal voltage	
Release Time	20 ms at nominal voltage	
Average Coil Resistance	7300 Ohm 20 °C +/- 15 %	
Rated Operational Voltage Limits	88121 V DC	
Protection Category	RTI	
Test Levels	Level A group mounting	
Safety Reliability Data	B10d = 100000	
Operating Position	Any position	
Net Weight	0.19 lb(US) (0.086 kg)	
Device Presentation	Complete product	

Environment

Dielectric Strength	1500 V AC between contacts with micro disconnection 2500 V AC between coil and contact with reinforced 2000 V AC between poles with basic
Product Certifications	EAC UL CSA
Standards	EN/IEC 61810-1 CSA C22.2 No 14 UL 508
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)
Vibration Resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 4 gn +/- 1 mm 10150 Hz)5 cycles not operating
Ip Degree Of Protection	IP40
Shock Resistance	10 gn 11 ms) in operation EN/IEC 60068-2-27 10 gn 11 ms) not operating EN/IEC 60068-2-27
Pollution Degree	3

Ordering and shipping details

Category	21127-ZELIO ICE CUBE RELAYS	
Discount Schedule	CP2	
Gtin	3606480626784	
Returnability	No	
Country Of Origin	CN	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.72 in (6.9 cm)
Package 1 Width	1.40 in (3.55 cm)
Package 1 Length	1.38 in (3.5 cm)

Package 1 Weight

2.98 oz (84.5 g)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc


Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Dimensions Drawings

Dimensions




Connections and Schema

Wiring Diagram



Wiring Diagram




Symbols shown in blue correspond to Nema marking.

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor $\cos\varphi)$



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.