Product data sheet





interface plug in relay, Harmony Electromechanical Relays, 10A, 1CO, clear cover, 12V DC

RXG15JD

! Discontinued on: Oct 9, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Interface relay
Product Or Component Type	Plug-in relay
Device Short Name	RXG
Contacts Type And Composition	1 C/O
[Ithe] Conventional Enclosed Thermal Current	10 A -40131 °F (-4055 °C)

Complementary

-		
[le] Rated Operational Current	10 A 30 V DC) UL 10 A 30 V DC) IEC 10 A 250 V AC) IEC	
	10 A 250 V AC) UL	
Electrical Durability	100000 cycles NO resistive at 55 °C 100000 cycles NC resistive at 55 °C	
Coil Resistance	270 Ohm +/- 10 %	
Shock Resistance	20 gn in operation 100 gn not in operation	
Mounting Position	Any position	
[Uc] Control Circuit Voltage	12 V DC	
Colour Of Cover	Transparent	
Drop-Out Voltage Threshold	>= 0.1 Uc DC	
Load Current	10 A 250 V AC	
Minimum Switching Capacity	500 mW at 100 mA, 5 V DC	
Maximum Switching Capacity	2500 VA	
Torque Value	7.08 lbf.in (0.8 N.m)	
Insulation Resistance	1000 MOhm at 500 V DC	
Mechanical Durability	10000000 cycles	
Safety Reliability Data	B10d = 100000	
Overvoltage Category	III	
Maximum Switching Voltage	250 V AC 30 V DC	
Protection Category	RTI	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Operating Rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load	
Utilisation Coefficient	20 %	
Pollution Degree	2	
[Ui] Rated Insulation Voltage	250 V IEC 300 V CSA 300 V UL	
Dielectric Strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation	
Test Levels	Level A group mounting	
Device Presentation	Complete product	
Contacts Material	Silver alloy (AgSnO2In2O3)	
Net Weight	0.04 lb(US) (0.018 kg)	

Environment

Ziivii diiiidit		
Standards	CSA C22.2 No 14 IEC 61810-1 UL 508	
Product Certifications	CSA CE EAC UL DNV-GL	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	
Ip Degree Of Protection	IP40	
Relative Humidity	1085 %	
Vibration Resistance	3 gn +/- 0.75 mm 10150 Hz)in operation 5 gn +/- 0.75 mm 10150 Hz)not in operation	

Ordering and shipping details

Category	US10CP221127	
Discount Schedule	nt Schedule 0CP2	
Gtin	3606480688942	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.36 in (3.45 cm)
Package 1 Width	3.64 in (9.25 cm)
Package 1 Length	3.39 in (8.6 cm)
Package 1 Weight	7.97 oz (226 g)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions








Connections and Schema


Wiring Diagram



Performance Curves

Performance Curves

Maximum Switching Capacity



X: Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

Life Expectancy

Resistive Load




X: Contact Current (A)

Y: Operating Cycle Number

Life Expectancy

Inductive Load




- X : Contact Current (A)
- Y: Operating Cycle Number

NOTE: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Coil Operating Range

DC Coil Operating Range VS Ambient Temperature



- X : Ambient temperature (°C)
- Y: Coil voltage (U/Uc)
- (1) Permitted operating range area