Product data sheet





Circuit breaker accessory, PowerPacT L, motor operator, MF, 380VAC to 415VAC, 50/60Hz

S432642

! Discontinued on: Mar 6, 2023

! Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Motor mechanism
Range Of Product	PowerPact L
Device Application	Control

Complementary

[Uc] Control Circuit Voltage	380 V AC 50 Hz 415 V AC 60 Hz
Tightening Torque	12.39 17.70 lbf in (1.4 2.N m)

Environment

Product Certifications	CSA	
	UL Listed	

Ordering and shipping details

Category	US10DE201103
Discount Schedule	0DE2
Gtin	3606486289402
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.00 lb(US) (2.268 kg)

Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov