

Product data sheet

Specifications



servo motor SH3 100
2,94Nm,nokey,multi,brake,
90°conn.IP65/IP67,6k RPM

SH31001M02F2200

Main

Range Compatibility	PacDrive 3
Product Or Component Type	Servo motor
Device Short Name	SH3.....M

Complementary

Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115...480 V
Phase	Three phase
Continuous Stall Current	1.8 A
Continuous Stall Torque	26.02 lbf.in (2.94 N.m) 115...480 V three phase
Continuous Power	660 W
Peak Stall Torque	84.97 lbf.in (9.6 N.m) 115...480 V three phase
Nominal Output Power	210 W 115 V single phase 410 W 230 V single phase 790 W 400 V three phase 930 W 480 V three phase
Nominal Torque	24.78 lbf.in (2.8 N.m) 115 V single phase 23.99 lbf.in (2.71 N.m) 230 V single phase 22.30 lbf.in (2.52 N.m) 400 V three phase 22.30 lbf.in (2.52 N.m) 480 V three phase
Nominal Speed	625 rpm 115 V single phase 1250 rpm 230 V single phase 2500 rpm 400 V three phase 3000 rpm 480 V three phase
Maximum Current Irms	6.3 A
Shaft End	Smooth shaft
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Key Width	0.24 in (6 mm)
Ip Degree Of Protection	IP65 motor: conforming to EN/IEC 60034-5 IP65 shaft bushing: conforming to EN/IEC 60034-5 IP67 housing: conforming to EN/IEC 60034-5
Encoder Type	Absolute multiturn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	79.66 lbf.in (9 N.m)
Mounting Support	International standard flange

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Straight connector
Torque Constant	1.63 N.m/A 248 °F (120 °C)
Back Emf Constant	115 V/krpm 68 °F (20 °C)
Number Of Motor Poles	4
Rotor Inertia	2.018 kg.cm²
Stator Resistance	13.9 Ohm
Stator Inductance	99.15 mH
Maximum Radial Force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm
Maximum Axial Force Fa	160 N
Type Of Cooling	Natural convection
Length	7.85 in (199.5 mm)
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9.0 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Net Weight	10.58 lb(US) (4.8 kg)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------