Product data sheet

Specification





single phase relay, Harmony Solid State Relays, 50A, DIN rail mount, zero voltage switching, input 4 to 32V DC, output 48 to 660V AC

SSP1A450BD

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 38.55 USD

Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Solid state relay up to 50 A
Device Short Name	SSP1
Mounting Support	Panel
Number Of Phases	1 phase
Line Rated Current	50 A
Solid State Output Type	Zero voltage switching SCR output
Output Switching Mode	Zero voltage switching

Complementary

Minimum Switching Voltage	4 V DC turn-on
Maximum Switching Voltage	1 V DC turn-off
Response Time	0.5 cycle (turn-on)
	0.5 cycle (turn-off)
Input Current	712 mA
Load Current	0.1550 A
Transient Overvoltage	1200 V
Surge Current	625 A 16.6 ms
Maximum I ² T For Fusing	1770 A ² .s for 10 ms at 50 Hz
	1629 A ² .s for 8.33 ms at 60 Hz
Co-Ordination Type	Type 1 - 40 A miniature circuit breaker (MCB) B
	Type 2 - 32 A miniature circuit breaker (MCB) B
Maximum Leakage Current	1 mA off-state
Maximum Voltage Drop	<1.15 V on-state
Dv/Dt	500 V/μs off-state at maximum voltage
Power Factor	0.5 (with maximum load)
Motor Controller Rating	0.75 hp 120 V AC
	2 hp 240 V AC
	5 hp 480 V AC
Insulation Resistance	1000 MOhm at 500 V DC
Maximum Capacitance	8 pF for input/output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Dielectric Strength	4 kV AC for input/output 4 kV AC for input or output to case	
[Uimp] Rated Impulse Withstand Voltage	6 kV output to case 6 kV input to output	
Tightening Torque	1.51.7 N.m for input 22.2 N.m for output	
Connections - Terminals	Screw terminals 0.23.3 mm², AWG 24AWG 12) with cable end input Screw terminals 0.55.26 mm², AWG 20AWG 10) with cable end output Screw terminals 0.23.3 mm², AWG 24AWG 12) without cable end input Screw terminals 0.58.26 mm², AWG 20AWG 8) without cable end output Forked type tag connectors 9.2 x 4 mm input Ring lugs 9.2 x 4 mm input Forked type tag connectors 11.7 x 4.5 mm output Ring lugs 11.7 x 4.5 mm output	
Thermal Resistance	0.45 °C/W junction to case	
Led Indicator	LED, green input	
Ip Degree Of Protection	IP20	
Safety Reliability Data	B10d = 1731395 MTTFd = 1875.9 years	
Net Weight	3.15 oz (89.2 g)	
Device Presentation	Complete product	

Environment

Ambient Air Temperature For Operation	-40176 °F (-4080 °C)
Ambient Air Temperature For Storage	-40257 °F (-40125 °C)
Pollution Degree	2
Overvoltage Category	III
Product Certifications	CSA UL EAC CE
Marking	UL CSA EAC CE
Standards	CSA C22.2 No 14-13 IEC 60950-1 IEC 62314 UL 508

Ordering and shipping details

Category	US10CP222375	
Discount Schedule	0CP2	
Gtin	3606485441870	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.8 cm)

Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	2.64 in (6.7 cm)
Package 1 Weight	3.39 oz (96.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.92 lb(US) (3.14 kg)

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Dimensions Drawings

Dimensions

 $\frac{\text{mm}}{in.}$








- (1) Front view
- (2) Side view
- (3) Bottom view

Performance Curves

Derating Curves



A: Load Current (Arms)

B: Ambient Temperature (°C)

- (1) For Heatsink SSRHP07
- (2) For Heatsink SSRHD10
- (3) For Heatsink SSRHP17
- (4) No Heatsink