# **Product data sheet**





## Harmony, Universal plug-in relay, 10 A, 2 CO, with lockable test button, 110 V DC

RUMC21FD

! Discontinued on: Oct 9, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony Electromechanical Relays	
Series Name	Universal	
Product Or Component Type	Plug-in relay	
Device Short Name	RUM	
Contacts Type And Composition	2 C/O	
[Uc] Control Circuit Voltage	110 V DC	
[Ithe] Conventional Enclosed Thermal Current	10 A -40131 °F (-4055 °C)	
Status Led	Without	
Control Type	Lockable test button	
Utilisation Coefficient	20 %	

## Complementary

Shape Of Pin	Cylindrical
[Ui] Rated Insulation Voltage	250 V IEC
	300 V CSA
	300 V UL
[Uimp] Rated Impulse Withstand Voltage	4 kV 1.2/50 μs)
Contacts Material	AgNi
[le] Rated Operational Current	10 A at 277 V AC conforming to UL
	10 A at 30 V DC conforming to UL
	10 A at 30 V DC conforming to CSA
	5 A at 250 V AC (NC) conforming to IEC
	5 A at 28 V DC (NC) conforming to IEC
	10 A at 250 V AC (NO) conforming to IEC
	10 A at 28 V DC (NO) conforming to IEC
	10 A at 277 V AC conforming to CSA
Maximum Switching Voltage	250 V IEC
Resistive Rated Load	10 A 250 V AC
	10 A 28 V DC
Maximum Switching Capacity	2500 VA/280 W
Minimum Switching Capacity	170 mW 10 mA, 17 V
Operating Rate	<= 18000 cycles/hour no-load
	<= 1200 cycles/hour under load
Mechanical Durability	5000000 cycles
Electrical Durability	100000 cycles resistive

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Average Coil Consumption In W	1.4 W
Drop-Out Voltage Threshold	>= 0.1 Uc DC
Operate Time	20 ms at nominal voltage
Release Time	20 ms at nominal voltage
Average Coil Resistance	7300 Ohm 20 °C +/- 15 %
Rated Operational Voltage Limits	88121 V DC
Protection Category	RTI
Test Levels	Level A group mounting
Safety Reliability Data	B10d = 100000
Operating Position	Any position
Net Weight	0.19 lb(US) (0.086 kg)
Device Presentation	Complete product

## **Environment**

Dielectric Strength	1500 V AC between contacts with micro disconnection 2500 V AC between coil and contact with reinforced 2000 V AC between poles with basic	
Product Certifications	EAC UL CSA	
Standards	EN/IEC 61810-1 UL 508 CSA C22.2 No 14	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)	
Vibration Resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 4 gn +/- 1 mm 10150 Hz)5 cycles not operating	
Ip Degree Of Protection	IP40	
Shock Resistance	10 gn 11 ms) in operation EN/IEC 60068-2-27 10 gn 11 ms) not operating EN/IEC 60068-2-27	
Pollution Degree	3	

# Ordering and shipping details

Category	US10CP221127	
Discount Schedule	0CP2	
Gtin	3606480626623	
Returnability	No	
Country Of Origin	CN	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.46 in (3.7 cm)
Package 1 Width	1.50 in (3.8 cm)
Package 1 Length	2.83 in (7.2 cm)

Package 1 Weight	3.35 oz (95.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.57 in (4.0 cm)
Package 2 Width	5.71 in (14.5 cm)
Package 2 Length	7.80 in (19.8 cm)
Package 2 Weight	32.66 oz (926.0 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	60
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	13.57 lb(US) (6.154 kg)

## Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Apr 25, 2024


## **Product data sheet**

## **RUMC21FD**

**Dimensions Drawings** 

### **Dimensions**






Connections and Schema

### Wiring Diagram

### Wiring Diagram




Symbols shown in blue correspond to Nema marking.

#### RUMC21FD

#### Performance Curves

#### **Electrical Durability of Contacts**


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor  $\cos \phi$ )



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC
Y Current DC

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.