Product data sheet

Specification





interface plug in relay, Harmony Electromechanical Relays, 5A, 2CO, lockable test but to n, 24V AC

RXG21B7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 7.32 USD

Main

Range Of Product	Harmony Electromechanical Relays	
Series Name	Interface relay	
Product Or Component Type	Plug-in relay	
Device Short Name	RXG	
Contacts Type And Composition	2 C/O	
[Ithe] Conventional Enclosed Thermal Current	5 A -40131 °F (-4055 °C)	
Local Signalling	Flag	

Complementary

Status Led	Without
[le] Rated Operational Current	5 A 30 V DC) UL 5 A 30 V DC) IEC 5 A 250 V AC) IEC 5 A 250 V AC) UL
Electrical Durability	100000 cycles NO resistive at 55 °C 100000 cycles NC resistive at 55 °C
Coil Resistance	260 Ohm +/- 10 %
Shock Resistance	20 gn in operation 100 gn not in operation
Mounting Position	Any position
Average Consumption In Va	0.82 VA 60 Hz
Control Circuit Voltage Limits	0.81.1 Uc AC
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
Colour Of Cover	Standard
Drop-Out Voltage Threshold	>= 0.3 Uc AC
Load Current	5 A 250 V AC
Minimum Switching Capacity	50 mW at 10 mA, 5 V DC
Maximum Switching Capacity	1250 VA
Control Type	Lockable test button
Torque Value	7.08 lbf.in (0.8 N.m)
Insulation Resistance	1000 MOhm at 500 V DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical Durability	10000000 cycles	
Safety Reliability Data	B10d = 100000	
Overvoltage Category	III	
Maximum Switching Voltage	250 V AC 30 V DC	
Protection Category	RTI	
Operating Rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load	
Utilisation Coefficient	20 %	
Pollution Degree	2	
[Ui] Rated Insulation Voltage	250 V IEC 300 V CSA 300 V UL	
Dielectric Strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation 3000 V AC between poles with basic insulation	
Test Levels	Level A group mounting	
Device Presentation	Complete product	
Contacts Material	Silver alloy (AgSnO2In2O3)	
Net Weight	0.04 lb(US) (0.02 kg)	

Environment

Standards	UL 508 IEC 61810-1 CSA C22.2 No 14
Product Certifications	CSA UL EAC CE DNV-GL
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Ip Degree Of Protection	IP40
Relative Humidity	1085 %
Vibration Resistance	3 gn +/- 0.75 mm 10150 Hz)in operation 5 gn +/- 0.75 mm 10150 Hz)not in operation

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
Gtin	3606480688997
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.40 in (1.016 cm)

Package 1 Width	1.30 in (3.302 cm)	
Package 1 Length	1.70 in (4.318 cm)	
Package 1 Weight	0.64 oz (18.144 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	1.38 in (3.5 cm)	
Package 2 Width	3.27 in (8.3 cm)	
Package 2 Length	3.58 in (9.1 cm)	
Package 2 Weight	7.80 oz (221 g)	
Unit Type Of Package 3	S01	
Number Of Units In Package 3	200	
Package 3 Height	5.91 in (15 cm)	
Package 3 Width	5.91 in (15 cm)	
Package 3 Length	15.75 in (40 cm)	
Package 3 Weight	10.56 lb(US) (4.79 kg)	

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions








RXG21B7

Connections and Schema


Wiring Diagram



Performance Curves

Performance Curves

Maximum Switching Capacity



X: Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

Life Expectancy

Resistive Load



X: Contact Current (A)


Y: Operating Cycle Number

Life Expectancy

Inductive Load

Product data sheet


RXG21B7



- X : Contact Current (A)
 Y : Operating Cycle Number
- **NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Coil Operating Range

AC Coil Operating Range VS Ambient Temperature



- X : Ambient temperature (°C)
- Y: Coil voltage (U/Uc)
- (1) Permitted operating range area