

Price** : 792.00 USD



⚠ Discontinued

SE8650U0B11 has not been replaced. Please contact your customer care center for more information.

Main

Range	EcoStruxure Building Expert
Product name	SE8000 Series
Device short name	SE8600
Product or component type	Roof top unit
Sensor type	10 kOhm T2 NTC thermistor measurement range: +/- 0.1 °C Single point calibrated bulk polymer RH sensor measurement range: +/- 5 %
Colour tint	White

Complementary

Device application	Staging equipment
[Us] rated supply voltage	24 V AC 50/60 Hz +/- 15 %
Network frequency	50 Hz 60 Hz
Communication port protocol	BACnet MS/TP
Function available	Economiser not included Scheduling Humidity control
Setpoint range cooling	12...37.5 °C for cooling 4.5...32 °C for heating
Temperature display range	-40...122 °F (-40...50 °C)
Measurement accuracy	+/- 0.5 °C temperature +/- 5 % humidity (20...80 % RH non-condensing)
Discrete input type	2 discrete input
Analogue input type	5 analog input 0...10 V
Number of outputs	4 analog 5 discrete
Output voltage	0...10 V DC <= 5 mA analog output
Surface finish	Matt
Surface treatment	Untreated
AWG gauge	AWG 22...AWG 18
Width	3.39 in (86 mm)
Depth	0.98 in (25 mm)
Height	4.72 in (120 mm)

Product weight	11.99 oz (340 g)
Market segment	Residential Non-critical buildings Buildings Healthcare Lodging Hotel School Office

Environment

Dehumidification setpoint range	30...95 %
Relative humidity	0...75 %
Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	-22...122 °F (-30...50 °C)
Standards	IEC 61326-1: 2005 FCC part 15 subpart C RSS 210 issue 8 FCC part 15 subpart B ICES-003 EN 60950-1: 2006/A2 EN 60950-1: 2013 ETSI EN 301 489-1: v1.9.2
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive 2014/53/EU - radio equipment directive

Ordering and shipping details

Category	21009 - SBS ROOM CONTROLLERS SE8000
Discount Schedule	DE10
GTIN	00785901643128
Nbr. of units in pkg.	1
Package weight(Lbs)	0.75
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
---------------------------	--