Product data sheet

Specifications



Controller, Modicon M171/172/173, optimized blind 22 IO, Modbus

TM171OBM22R

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 167.28 USD

Main

Range Of Product	Modicon M171/M172
Product Or Component Type	Controller
Product Specific Application	HVAC and pumping solution
Variant	Programmable
Total Inputs/Outputs	22
Discrete Input Number	6
Discrete Output Number	1 open collector 3 relay outputs SPST with same common 2 relay outputs SPST with independent common
Discrete Output Current	2 A relay
Analogue Input Number	2 configurable 3 analog input NTC
Analogue Output Number	3 voltage 010 V 2 PWM/PPM 20 kHz, 12 V, 35 mA

Complementary

Number Of Port	1 LAN expansion bus 1 RS485 - screw terminal block Modbus serial link)
Input/Output Number	5 analog output
	6 digital input
	5 analog input
	6 digital output
Discrete Input Logic	Sink or source (positive/negative)
Contacts Usage	Volt-free contacts
Analogue Input Type	voltage 05 V ratiometric)
	voltage 010 V
	current 020 mA/420 mA
	voltage 01 V
	temperature probe - 50100 °C 0.1 °C
Sensor Power Supply	12 V DC 85 mA
	5 V DC 20 mA
[Us] Rated Supply Voltage	24 V
	1224 V AC
Realtime Clock	Built-in clock at -4131 °F (-2055 °C)
Display Type	Four 7-segment display units
Overvoltage Category	11

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Local Signalling	6 LEDs (red) 5 LEDs (green) for programmable 7 LEDs (amber)
Mounting Support	DIN rail
Width	2.76 in (70.2 mm)
Height	3.43 in (87 mm)
Depth	2.43 in (61.6 mm)
Net Weight	0.42 lb(US) (0.19 kg)

Environment

Directives	2006/95/EC - low voltage directive 86/188/EEC - physical agents (noise) directive
Standards	EN 60730-1 UL 60730-1 IEC 61000-4-6 IEC 61000-4-3 UL 60730-2-9 IEC 61000-4-4 IEC 61000-4-2 CSA E60730-2-9 IEC 61000-4-5 EN 60068-2-6 Fc IEC 61000-4-11 EN 60730-2-9 EN 60068-2-27 CAN/CSA-E60730-1 UL94 (material V0)
Product Certifications	EAC CSA RCM CE cURus
Ambient Air Temperature For Operation	-4131 °F (-2055 °C) UL 60730-1
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	1090 % non-condensing
Ip Degree Of Protection	IP20
Pollution Degree	2

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
Gtin	3606480752742
Returnability	No
Country Of Origin	US

Packing Units

<u>~</u>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.20 in (13.200 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	7.28 in (18.500 cm)
Package 1 Weight	8.85 oz (251.000 g)

Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	3.81 lb(US) (1.726 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Resource performance

Upgradeable Through Digital Modules And Upgraded Components

Well-being performance




Rohs Exemption Information Yes

Certifications & Standards

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions




Product data sheet


Mounting and Clearance

Mounting and Clearance

Clearance



Misplacement






Product data sheet


Connections and Schema


Power Supply




(1) Type T fuse (Controller: 1.25 A , Expansion: 1 A)

Wiring Diagram







N: Neutral

GND : Ground

BK : Black

BU : Blue

RD : Red

AI : Analogue input AO : Analogue output

DI : Digital input

DO : Digital output