


Product data sheet

Specifications



Compact I/O expansion block, Modicon TM5, 8 AI, 8 AO, 0 10 V, 4 20 mA, 12 bits

TM5CAI8O8CVL

⚠ Discontinued - Service only

⚠ Discontinued on: Dec 2, 2020

⚠ To be end-of-service on: Sep 1, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon TM5
Product Or Component Type	Compact I/O expansion block
Enclosure Material	Plastic
Color	White
Input/Output Number	16
Input/Output Number Of Splitter Box	8 I + 8 O
Number Of Modules	Analog input 2 x 4 Analog output 2 x 4
Analogue Input Number	8
Analogue Input Range	4...20 mA 0...20 mA +/- 10 V
Analogue Input Resolution	12 bits current 11 bits + sign voltage
Analogue Output Number	8
Analogue Output Type	Voltage 4 Current 4
Analogue Output Range	0...20 mA +/- 10 V

Complementary

Input Filtering	<= 50 ms not configurable
Sampling Duration	20 ms input/output for the whole module 5 ms input/output per channel
Response Time	<= 1 ms status change output
Maximum Leakage Current	5 µA when switched off) output
Protection Type	Short-circuit output
Isolation	500 Vrms AC insulation between channel and bus No insulation between channels
Current Consumption	8 mA 5 V DC bus 217 mA 24 V DC input/output
Power Dissipation In W	5.25 W

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Local Signalling	for power supply 4 LEDs (green) for power supply 4 LEDs (red) for output status 8 LEDs (yellow) for input status 8 LEDs (green)
Electrical Connection	Removable spring terminal block
Surge Withstand	0.5 kV differential mode 24 V DC EN/IEC 61000-4-5 1 kV common mode 24 V DC EN/IEC 61000-4-5
Mounting Support	DIN rail
Net Weight	0.55 lb(US) (0.25 kg)

Environment

Standards	CSA C22.2 No 213 UL 508 CSA C22.2 No 142 IEC 61131-2
Product Certifications	C-tick UL GOST-R CSA
Marking	CE
Ambient Air Temperature For Operation	14...122 °F (-10...50 °C) vertical installation) 14...140 °F (-10...60 °C) horizontal installation)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Relative Humidity	5...95 % without condensation
Ip Degree Of Protection	IP20IEC 61131-2
Pollution Degree	2 IEC 60664
Operating Altitude	0...6561.68 ft (0...2000 m)
Storage Altitude	0.00...9842.52 ft (0...3000 m)
Vibration Resistance	1 gn 8.4...150 Hz DIN rail 3.5 mm 5...8.4 Hz DIN rail
Shock Resistance	15 gn 11 ms
Resistance To Electrostatic Discharge	4 kV on contact EN/IEC 61000-4-2 8 kV in air EN/IEC 61000-4-2
Resistance To Electromagnetic Fields	0.91 V/m (1 V/m) 2...2.7 GHz EN/IEC 61000-4-3 9.14 V/m (10 V/m) 80...2000 MHz EN/IEC 61000-4-3
Resistance To Fast Transients	1 kV EN/IEC 61000-4-4 I/O) 1 kV EN/IEC 61000-4-4 shielded cable) 2 kV EN/IEC 61000-4-4 power lines)
Electromagnetic Compatibility	EN/IEC 61000-4-6
Disturbance Radiated/Conducted	CISPR 11 zone B - class A

Ordering and shipping details

Category	US1PC1222532
Discount Schedule	PC12
Gtin	3595864145143
Returnability	No
Country Of Origin	AT

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	4.33 in (11.0 cm)
Package 1 Weight	9.95 oz (282.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.33 lb(US) (4.23 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance


✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Presentation

TM5 Compact I/O Module




N°	Designation
1	Analog Input electronic module / 4 Analog Inputs
2	Analog Input electronic module / 4 Analog Inputs
3	Dummy Module
4	Analog Output electronic module / 4 Analog Outputs
5	Analog Output electronic module / 4 Analog Outputs

Dimensions Drawings

Compact I/O Module


Dimensions




Mounting and Clearance

TM5 System

Spacing Requirements




Mounting on a DIN Rail



Connections and Schema


TM5 System Wiring Recommendations

Wire Sizes to Use with the Removable Spring Terminal Blocks

				
mm ²	0,08...2,5	0,25...2,5	0,25...1,5	2 x 0,25...2 x 0,75
AWG	28...14	24...14	24...16	2 x 24...2 x 18

Analog Input 4AI ±10 V


Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- U Voltage

Analog Input 4AI 0-20 mA / 4-20 mA


Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- I Current

Analog Output 4AO ±10 V


Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- U Voltage

Analog Output 4AO 0-20 mA

Wiring Diagram



1 Internal electronics

2 24 Vdc I/O power segment integrated into the bus bases

I Current