


Product data sheet

Specifications



compact PLC base Twido - 100..240 V AC supply - 24 I 24 V DC - 16 O

TWDLCAE40DRF

⚠ Discontinued on: Mar 15, 2022

⚠ Discontinued

Main

Range Of Product	Twido
Product Or Component Type	Compact base controller
Concept	Transparent Ready
Discrete I/O Number	40
Discrete Input Number	24
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Discrete Output Number	14 relay 2 transistor
[Us] Rated Supply Voltage	100...240 V AC
Maximum Number Of I/O Expansion Module	7
Use Of Slot	Memory cartridge
Data Backed Up	Internal RAM external battery TSXPLP01, 3 years
Integrated Connection Type	Power supply Non isolated serial link mini DIN, Modbus/character mode master/slave RTU/ASCII RS485) half duplex, 38.4 kbit/s Serial link interface adaptor RS232C/RS485) Ethernet TCP/IP RJ45, , 10/100 Mbit/s, 1 twisted pair transparent ready class A10
Complementary Function	PID Event processing

Complementary

Discrete Input Logic	Sink or source
Input Voltage Limits	20.4...26.4 V
Discrete Input Current	11 mA I0.0 to I0.1 11 mA I0.6 to I0.7 7 mA I0.2 to I0.5 7 mA I0.8 to I0.23
Input Impedance	2100 Ohm I0.0 to I0.1 2100 Ohm I0.6 to I0.7 3400 Ohm I0.2 to I0.5 3400 Ohm I0.8 to I0.23
Filter Time	150 µs + programmed filter time for I0.6 to I0.23 at state 0 35 µs + programmed filter time for I0.0 to I0.5 at state 1 40 µs + programmed filter time for I0.0 to I0.5 at state 0 40 µs + programmed filter time for I0.6 to I0.23 at state 1
Insulation Between Channel And Internal Logic	1500 Vrms for 1 minute

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Insulation Resistance Between Channel	None
Minimum Load	0.1 mA
Contact Resistance	30000 µOhm
Load Current	2 A 240 V AC inductive 30 cyc/mn relay output 2 A 240 V AC resistive 30 cyc/mn relay output 2 A 30 V DC inductive 30 cyc/mn relay output 2 A 30 V DC resistive 30 cyc/mn relay output
Mechanical Durability	20000000 cycles relay output
Electrical Durability	100000 cycles relay output
Current Consumption	128 mA 24 V DC at state 1 128 mA 24 V DC state 1 + input ON 170 mA 5 V DC at state 0 240 mA 5 V DC state 1 + input ON 5 mA 24 V DC at state 0 90 mA 5 V DC at state 1
I/O Connection	Non-removable screw terminal block
Maximum Input/Output Number	152 removable screw terminal block with I/O expansion module 208 spring terminal block with I/O expansion module 264 HE-10 connector with I/O expansion module
Network Frequency	50/60 Hz
Supply Voltage Limits	85...264 V
Network Frequency Limits	47...63 Hz
Power Supply Output Current	0.4 A 24 V DC sensors
Input Current	790 mA
Inrush Current	35 A
Protection Type	Power protection internal fuse
Power Consumption In Va	65 VA 100 V 77 VA 264 V
Insulation Resistance	> 10 MOhm at 500 V, between I/O and earth terminals > 10 MOhm at 500 V, between supply and earth terminals
Program Memory	3000 instructions
Exact Time For 1 Kinstruction	1 ms
System Overhead	0.5 ms
Memory Description	Internal RAM, 128 counters, no floating, no trigonometrical Internal RAM, 128 timers, no floating, no trigonometrical Internal RAM, 256 internal bits, no floating, no trigonometrical Internal RAM, 3000 internal words, no floating, no trigonometrical Internal RAM, double words, no floating, no trigonometrical Internal RAM, floating, trigonometrical
Free Slots	1
Realtime Clock	With <= 30 s/month 30 days
Port Ethernet	10BASE-T/100BASE-TX
Communication Service	BOOTP client, Ethernet TCP/IP Modbus messaging, Ethernet TCP/IP
Positioning Functions	PWM/PLS 2 7 kHz
Counting Input Number	2 20000 Hz 32 bits 4 5000 Hz 16 bits
Analogue Adjustment Points	1 point adjustable from 0 to 511 points 1 point adjustable from 0...1023

Status Led	1 LED (Green) PWR 1 LED (Green) RUN 1 LED per channel (Green) I/O status 1 LED (Red) module error (ERR) 1 LED user pilot light (STAT) 1 LED 10 or 100 Mbit/s rate (LACT) 1 LED Ethernet status (LAN ST)
Depth	2.76 in (70 mm)
Height	3.74 in (95 mm)
Width	3.54 in (90 mm)
Net Weight	1.16 lb(US) (0.525 kg)

Environment

Immunity To Microbreaks	10 ms
Dielectric Strength	1500 V for 1 minute, between I/O and earth terminals 1500 V for 1 minute, between supply and earth terminals
Product Certifications	UL CSA
Marking	CE
Ambient Air Temperature For Operation	32...131 °F (0...55 °C)
Ambient Air Temperature For Storage	-13...158 °F (-25...70 °C)
Relative Humidity	30...95 % without condensation
Ip Degree Of Protection	IP20
Operating Altitude	0...6561.68 ft (0...2000 m)
Storage Altitude	0.00...9842.52 ft (0...3000 m)
Vibration Resistance	0.075 mm 10...57 Hz 35 mm symmetrical DIN rail 1 gn 57...150 Hz 35 mm symmetrical DIN rail 1.6 mm 2...25 Hz plate or panel with fixing kit 4 gn 25...100 Hz plate or panel with fixing kit
Shock Resistance	15 gn 11 ms

Ordering and shipping details


Category	22531-PLCS, TWIDO, TWD
Discount Schedule	PC12
Gtin	3595863816020
Returnability	No
Country Of Origin	ID

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings


Dimensions




* 8.5 mm (0.33 in) when the clamp is pulled out.

Mounting and Clearance

Minimum Clearances for a Compact Base and Expansion I/O Modules




Mounting Hole Layout




Connections and Schema

AC Power Supply Wiring Diagram




DC Source Inputs Wiring Diagrams

External Power




Internal Power




Max current: 400mA.

DC Sink Inputs Wiring Diagrams

External Power




Internal Power



Max current: 400mA.


Relay and Transistor Outputs Wiring Diagram



Performance Curves

Performance Curves

I/O Usage Limits



- (1) Limit for TWDLCAE40DRF, TWDLCAE40DRF, TWDLCAE40DRF and TWDLCAE40DRF
- (2) All compact bases