# Product data sheet

Specifications





# heat sink, Harmony Solid State Relays, thermal resistance 1 degree C W

SSRHP10

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 32.90 USD

### Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Heat sink

### Complementary

Product Compatibility1 solid state relay SSP panelThermal Resitance1 °C/WMounting SupportPanelMaterialAluminiumSurface FinishBlack anodizedSurface And Useful Surface220.88 in² (1425 cm²)Number Of Mounting Holes6 UNC 8-32Tightening Torque15.0519.47 lbf.in (1.72.2 N.m)Sale Per Indivisible Quantity1Width3.00 in (76.2 mm)Height5.20 in (132.1 mm)Depth2.37 in (60.2 mm)	
Mounting SupportPanelMaterialAluminiumSurface FinishBlack anodizedSurface And Useful Surface220.88 in² (1425 cm²)Number Of Mounting Holes6 UNC 8-32Tightening Torque15.0519.47 lbf.in (1.72.2 N.m)Sale Per Indivisible Quantity1Width3.00 in (76.2 mm)Height5.20 in (132.1 mm)	
Material   Aluminium     Surface Finish   Black anodized     Surface And Useful Surface   220.88 in² (1425 cm²)     Number Of Mounting Holes   6 UNC 8-32     Tightening Torque   15.0519.47 lbf.in (1.72.2 N.m)     Sale Per Indivisible Quantity   1     Width   3.00 in (76.2 mm)     Height   5.20 in (132.1 mm)	
Surface FinishBlack anodizedSurface And Useful Surface220.88 in² (1425 cm²)Number Of Mounting Holes6 UNC 8-32Tightening Torque15.0519.47 lbf.in (1.72.2 N.m)Sale Per Indivisible Quantity1Width3.00 in (76.2 mm)Height5.20 in (132.1 mm)	
Surface And Useful Surface   220.88 in² (1425 cm²)     Number Of Mounting Holes   6 UNC 8-32     Tightening Torque   15.0519.47 lbf.in (1.72.2 N.m)     Sale Per Indivisible Quantity   1     Width   3.00 in (76.2 mm)     Height   5.20 in (132.1 mm)	
Number Of Mounting Holes   6 UNC 8-32     Tightening Torque   15.0519.47 lbf.in (1.72.2 N.m)     Sale Per Indivisible Quantity   1     Width   3.00 in (76.2 mm)     Height   5.20 in (132.1 mm)	
Tightening Torque 15.0519.47 lbf.in (1.72.2 N.m)   Sale Per Indivisible Quantity 1   Width 3.00 in (76.2 mm)   Height 5.20 in (132.1 mm)	
Sale Per Indivisible Quantity 1   Width 3.00 in (76.2 mm)   Height 5.20 in (132.1 mm)	
Width     3.00 in (76.2 mm)       Height     5.20 in (132.1 mm)	
Height     5.20 in (132.1 mm)	
<b>Denth</b> 2 37 in (60.2 mm)	
2.57 in (00.2 min)	
Net Weight     1.37 lb(US) (0.620 kg)	

### Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
Gtin	3606480580239
Returnability	No
Country Of Origin	US

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	3.78 in (9.6 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	17.53 oz (497.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	22
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	24.12 lb(US) (10.94 kg)

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

# Product data sheet

#### **Dimensions Drawings**

#### Dimensions

