

VBD1

TeSys Vario - switch disconnecter - 32 A - on door

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 219.00 USD



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VBD
Device application	Preventive maintenance
Product or component type	Switch disconnecter
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	DC AC
Control type	Rotary handle
Rotary handle mounting style	Direct
Handle colour	Black
Handle front plate colour	Black
Suitability for isolation	Yes

Complementary

Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1
Mounting support	Handle door Switch door
Fixing mode	Hole 0.89 in (22.5 mm) handle
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	32 A

[Ithe] conventional enclosed thermal current	25 A
[Ie] rated operational current	21.8 A AC-23 Ue: 400 V
Rated operational power in W	11 kW 500 V AC-23A) 15 kW 690 V AC-23A) 7.5 kW 500 V AC-3) 7.5 kW 690 V AC-3) 1.5 kW 230...240 V AC-3) 5.5 kW 230...240 V AC-23A) 11 kW 400...415 V AC-23A) 7.5 kW 400...415 V AC-3)
Intermittent duty class	30
Making capacity (I Rms)	320 A 400 V AC-21A 320 A 400 V AC-22A 320 A 400 V AC-23A
[Icm] rated short-circuit making capacity	1 kA 400 V at Ipeak
[Icw] rated short-time withstand Rms current	384 A 400 V 1 s
Rated conditional short-circuit current	10 kA 400 V 35 A aM 10 kA 400 V 35 A gG
Breaking capacity	250 A 400 V AC-21A) 250 A 400 V AC-22A) 250 A 400 V AC-23A)
Device composition	Switch Handle
Mechanical durability	100000 cycles
Electrical durability	100000 cycles AC-21 30000 cycles DC-1...5
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.01 in ² (6 mm ²) flexible - with cable end
Tightening torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Handle front plate dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Net weight	0.47 lb(US) (0.215 kg)

Environment

Standards	IEC 60947-3
Product certifications	UL GL CSA CCC
Protective treatment	TC
IP degree of protection	IP20 IEC 60529 IP65
Mechanical robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901528920
Package weight(Lbs)	0.21 kg (0.47 lb(US))
Returnability	No
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------