


Product data sheet

Specifications



braking resistor, Altivar, 8Ohms, 1.1kW, IP20

VW3A7735

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 525.57 USD

Main

Range Compatibility	Altivar Process ATV900 Altivar Machine ATV340 Altivar Machine ATV320
Product Or Component Type	Braking resistor
Ohmic Value	8 Ohm
[Ue] Rated Operational Voltage	24 V DC 250 V AC

Complementary

Product Compatibility	Variable speed drive ATV930 wall mount 55 kW 380...480 V light cycle Variable speed drive ATV930 wall mount 15 kW 200...240 V light cycle Variable speed drive ATV950 wall mount 55 kW 380...480 V light cycle Variable speed drive ATV930 wall mount 15 kW 200...240 V medium cycle Variable speed drive ATV340 45 kW 380...480 V light cycle Variable speed drive ATV320 11 kW 200...240 V
Duty Cycle	Light cycle (heavy duty) <0.8 s braking with 150 % braking torque for a 40 s cycle Light cycle (normal duty) <0.8 s braking with 120 % braking torque for a 40 s cycle Medium cycle (normal duty) <4 s braking with 135 % braking torque for a 40 s cycle Medium cycle (heavy duty) <4 s braking with 165 % braking torque for a 40 s cycle
Average Power Available	1.1 kW 122 °F (50 °C)
Electrical Connection	terminal <= 35 mm² / AWG 3 drive terminal <= 4 mm² / AWG 10 temperature control switch
Protection Type	Thermal protection via drive or temperature control switch 120 °C
Width	7.48 in (190 mm)
Height	25.20 in (640 mm)
Depth	7.09 in (180 mm)
Net Weight	9.92 lb(US) (4.5 kg)

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Storage	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Operation	32...122 °F (0...50 °C)

Ordering and shipping details

Category	US1CP4E22209
Discount Schedule	CP4E
Gtin	3606480802294

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.84 in (25.000 cm)
Package 1 Width	7.87 in (20.000 cm)
Package 1 Length	25.59 in (65.000 cm)
Package 1 Weight	11.78 lb(US) (5.342 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	6
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	89.40 lb(US) (40.552 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)


Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Dimensions

Right Side and Front View



Dimensions in mm

A	B	C	A1	C1	Ø
190	180	640	170	380	6.6 x 9

Dimensions in in.


A	B	C	A1	C1	Ø
7.48	7.09	25.20	6.69	14.96	0.26 x 0.35

Mounting and Clearance

Mounting and Clearance




(1) Braking resistor



Connections and Schema

Recommended Schema

1 Braking Resistor




A1 : Drive or external braking unit

A2 : Braking resistor

PA, PB : Bus DC

2 Braking Resistors



A1 : Drive or external braking unit

A2 : Braking resistor

PA, PB : Bus DC