Product data sheet

Specifications





Connector module, Lexium 32i, connection for industrial connectors, CANopen, 2 DI, source, STO

VW3M9103

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 213.34 USD

Main

Range Of Product	Lexium 32i
Product Or Component Type	Connector module
Accessory / Separate Part Category	Connection accessories
Electrical Connection	Industrial connector

Complementary

Product Compatibility	Drive control unit LXM32i CANopen
Accessory / Separate Part Destination	Motor BMI with drive control unit Lexium 32i
Range Compatibility	Lexium 32i
Communication Interface	CANmotion CANopen DS402
Input/Output Type	2 discrete inputs
Discrete Input Logic	Source
Safety Function	STO (safe torque off)
Net Weight	0.49 lb(US) (0.222 kg)

Ordering and shipping details

Category	US1PC5618289
Discount Schedule	PC56
Gtin	3606480610806
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.27 in (8.3 cm)
Package 1 Width	4.61 in (11.7 cm)
Package 1 Length	6.69 in (17.0 cm)
Package 1 Weight	7.62 oz (216.0 g)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.81 lb(US) (3.09 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Connections and Schema

Connection of I/O Module for CANopen with Industrial Connectors



- (1) IN
- (2) OUT

Signal	Meaning
+24VDC	24 V signal power supply
0VDC	Reference potential to +24VDC
DIO	Digital input 0
DI1	Digital input 1
DI2	Digital input 2
DI3	Digital input 3
STO_A	Safety function STO
STO_COM	Reference potential for safety function STO
STO_B	Safety function STO
SHLD	Shield (grounded internally)
CAN_0V	Reference potential for CAN
CAN_H	CAN interface
CAN_L	CAN interface

Product data sheet

VW3M9103

Signal	Meaning
NC	Not connected