# **Product data sheet**

Specifications





# Harmony, pendant station, pistol grip, yellow, 2 push buttons

XACA201

Product availability: Stock - Normally stocked in distribution

Price\*: 150.00 USD

## Main

Range Of Product	Harmony XAC	
Product Or Component Type	Pendant control station	
Device Short Name	XACA pistol grip	

## Complementary

Control Station Type	Double insulated		
Enclosure Material	Polypropylene		
Control Type	Intuitive		
Electrical Circuit Type	Control circuit		
Enclosure Type	Complete ready for use		
Control Station Application	Control of single speed hoist motor		
Control Station Composition	2 push-buttons		
Control Button Type	First push-button 1 NO raise, slow Second push-button 1 NO lower, slow		
Product Compatibility	ZB2BE101 for each direction		
Mechanical Interlocking	With mechanical interlocking		
Control Station Colour	Yellow		
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end		
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 UL 508		
Product Certifications	CSA UL		
Protective Treatment	TH		
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)		
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)		
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6		
Shock Resistance	100 gn IEC 60068-2-27		
Overvoltage Category	Class II IEC 61140		
Ip Degree Of Protection	IP65 conforming to IEC 60529		
Ik Degree Of Protection	IK08 conforming to EN 50102		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical Durability	1000000 cycles			
Cable Entry	Rubber sleeve with stepped entry 0.280.59 in (715 mm)  A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A			
Contact Code Designation				
[Ithe] Conventional Enclosed Thermal Current	10 A			
[Ui] Rated Insulation Voltage	600 V 3)IEC 60947-1			
[Uimp] Rated Impulse Withstand Voltage	stand 6 kV IEC 60947-1			
Contact Operation	Slow-break			
Maximum Resistance Across Terminals	25 MOhm			
Operating Force	1315 N			
Short-Circuit Protection	10 A fuse protection cartridge gG			
Rated Operational Power In W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C			
Terminals Description Iso N°1	(13-14)NO			
Terminal Identifier	inal Identifier (11-12)NC (13-14)NO			
Net Weight	0.60 lb(US) (0.27 kg)			

# Ordering and shipping details

Category	US10CS222473
Discount Schedule	0CS2
Gtin	3389110645002
Returnability	Yes
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.95 in (7.500 cm)	
Package 1 Width	2.36 in (6.000 cm)	
Package 1 Length	10.63 in (27.000 cm)	
Package 1 Weight	8.89 oz (252.000 g)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	6	
Package 2 Height	5.91 in (15.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	4.01 lb(US) (1.820 kg)	
Unit Type Of Package 3	P06	

Number Of Units In Package 3	96
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	89.39 lb(US) (40.548 kg)

# **Contractual warranty**

Warranty 18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>9</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration			
Eu Rohs Directive				
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

## **Dimensions Drawings**

#### **Dimensions**




(1) Internal Ø

## **Product data sheet**

## **XACA201**

Connections and Schema

## Control of Single-Speed Reversing Motor




#### **XACA201**

#### Performance Curves

#### **Rated Operational Power**

#### AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current

(A) Current

#### **DC** Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	W	65	48	40