# **Product data sheet**

Specification





Pendant control station, Harmony XAC, plastic, yellow, 2 push buttons with 2NO+1NC, 1 emergency stop NC

XACA2913



#### Main

| Range Of Product          | Harmony XAC             |  |
|---------------------------|-------------------------|--|
| Product Or Component Type | Pendant control station |  |
| Device Short Name         | XACA                    |  |

### Complementary

| Control Station Type                  | Double insulated  |
|---------------------------------------|---|
| Enclosure Material                    | Polypropylene   |
| Electrical Circuit Type               | Control circuit   |
| Enclosure Type                        | Complete ready for use  |
| Control Station Application           | Control of 2-speed hoist motor  |
| Control Station Composition           | 2 push-buttons + 1 emergency stop   |
| Control Button Type                   | Stop push-button Ø 30 mm 1 NC latching First push-button 1 NC + 2 NO raise, slow-fast Second push-button 1 NC + 2 NO lower, slow-fast |
| Product Compatibility                 | ZB2BE102 for emergency stop<br>XENG1191 for each direction  |
| Mechanical Interlocking               | With mechanical interlocking  |
| Control Station Colour                | Yellow  |
| Connections - Terminals               | Screw clamp terminals, 1 x 0.51 x 2.5 mm² without cable end<br>Screw clamp terminals, 1 x 0.52 x 1.5 mm² with cable end               |
| Standards                             | UL 508<br>CSA C22.2 No 14<br>EN/IEC 60947-5-1<br>EN/IEC 60204-32  |
| Product Certifications                | CCC<br>GOST   |
| Protective Treatment                  | тн  |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C)  |
| Ambient Air Temperature For Storage   | -40158 °F (-4070 °C)  |
| Vibration Resistance                  | 15 gn 10500 Hz)IEC 60068-2-6  |
| Shock Resistance                      | 100 gn IEC 60068-2-27   |
| Overvoltage Category                  | Class II IEC 61140  |
| Ip Degree Of Protection               | IP65 conforming to IEC 60529  |
| Ik Degree Of Protection               | IK08 conforming to EN 50102   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



| Mechanical Durability                           | 1000000 cycles   |
|---|--|
| Cable Entry                                     | Rubber sleeve with stepped entry 0.311.02 in (826 mm)  |
| Contact Code Designation                        | A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A   |
| [Ithe] Conventional Enclosed<br>Thermal Current | 10 A   |
| [Ui] Rated Insulation Voltage                   | 600 V 3)   |
| [Uimp] Rated Impulse Withstand<br>Voltage       | 6 kV IEC 60947-1   |
| Contact Operation                               | Slow-break<br>Staggered  |
| Maximum Resistance Across<br>Terminals          | 25 MOhm  |
| Operating Force                                 | 18 N push-button<br>8 N emergency stop   |
| Short-Circuit Protection                        | 10 A fuse protection cartridge gG  |
| Rated Operational Power In W                    | 40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C |
| Terminals Description Iso N°1                   | (21-22)NC<br>(13-14)NO<br>(33-34)NO_CL   |
| Terminals Description Iso N°2                   | (11-12)NC  |
| Terminal Identifier                             | (13-14)NO<br>(11-12)NC   |
| Net Weight                                      | 1.26 lb(US) (0.57 kg)  |

## Ordering and shipping details

| Category          |               |  |
|-------------------|---------------|--|
| Discount Schedule |               |  |
| Gtin              | 3389110426847 |  |
| Returnability     | No            |  |
| Country Of Origin | CZ            |  |

## **Packing Units**

| Unit Type Of Package 1       | PCE                  |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 3.94 in (10.000 cm)  |
| Package 1 Width              | 4.33 in (11.000 cm)  |
| Package 1 Length             | 20.47 in (52.000 cm) |
| Package 1 Weight             | 24.60 oz (697.300 g) |
| Unit Type Of Package 2       | S04                  |
| Number Of Units In Package 2 | 6                    |
| Package 2 Height             | 11.81 in (30.000 cm) |
| Package 2 Width              | 15.75 in (40.000 cm) |

| Package 2 Length             | 23.62 in (60.000 cm)     |  |
|------------------------------|--------------------------|--|
| Package 2 Weight             | 10.64 lb(US) (4.828 kg)  |  |
| Unit Type Of Package 3       | P06                      |  |
| Number Of Units In Package 3 | 24                       |  |
| Package 3 Height             | 29.53 in (75.000 cm)     |  |
| Package 3 Width              | 31.50 in (80.000 cm)     |  |
| Package 3 Length             | 23.62 in (60.000 cm)     |  |
| Package 3 Weight             | 60.21 lb(US) (27.311 kg) |  |

### **Contractual warranty**

Warranty 18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration  |
| China Rohs Regulation     | China RoHS declaration   |
| Environmental Disclosure  | Product Environmental Profile  |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |
| Circularity Profile       | No need of specific recycling operations   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |