

Product data sheet

Specifications

SQUARE D



TeSys NEMA Sz 6 open starter, 3P, 120 VAC

T36HN13F7S

Discontinued on: Nov 11, 2020

End-of-service on: Dec 31, 2020

Discontinued

Main

Product	Starter
Range Of Product	TeSys N
Current Rating	540 A
Certifications	UL Listed CSA
Control Circuit Type	Separate control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	6
Control Circuit Voltage	120 V AC
Starter Type	Non reversing
Electrical Connection	Lugs ordered separately
Overload Type	Solid state Motor Logic class 10/20 180...540 A

Ordering and shipping details

Category	21199-TESYS N STARTERS SIZES 3 - 7
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov	