

# Product data sheet

Specifications



Pendant control station, Harmony XAC, plastic, yellow, 2 push buttons, 1 emergency stop, cable 10... 22mm, for XESD1291

XACB2291

! Discontinued

## Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACB

## Complementary

Control Station Type	Double insulated
Enclosure Material	Glass reinforced polyester
Electrical Circuit Type	Power circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of 2-speed hoist motor
Control Station Composition	2 push-buttons + 1 emergency stop
Control Button Type	Emergency stop push-button Ø 40 mm First push-button 2-pole raise, slow-fast Second push-button 2-pole lower, slow-fast
Product Compatibility	XESD1291 for reversing operation
Mechanical Interlocking	With mechanical interlocking
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32
Product Certifications	CSA type 4
Protective Treatment	TH
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Mechanical Durability	1000000 cycles
Cable Entry	Rubber sleeve with stepped entry 0.39...0.87 in (10...22 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ithe] Conventional Enclosed Thermal Current	12 A
[Uij] Rated Insulation Voltage	500 V 3)IEC 60947-1 600 VCSA
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Contact Operation	Snap action
Operating Force	17 N push-button
Short-Circuit Protection	10 A fuse protection cartridge aM
Rated Power In Hp	2 hp 240 V, CSA 3 hp 600 V, CSA 5 hp 400 V, CSA
Rated Operational Power In W	2200 W AC-3 240 V IEC 60947-3 appendix A 2200 W AC-3 400 V IEC 60947-3 appendix A 2200 W AC-4 240 V IEC 60947-3 appendix A 2200 W AC-4 400 V IEC 60947-3 appendix A
Electrical Durability	300000 cycles AC-3, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-3, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-3, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-4, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-3, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-4, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminal Identifier	(11-12)NC (13-14)NO

## Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
Gtin	3389110367225
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	10.63 in (27.0 cm)
Package 1 Weight	32.47 oz (920.5 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>