Specifications





logic controller, Modicon M241, 40 IO, relay, Ethernet

TM241CE40R

Product availability: Stock - Normally stocked in distribution facility

Price*: 569.00 USD

Main

| in an i | |
|---------------------------|--|
| Range Of Product | Modicon M241 |
| Product Or Component Type | Logic controller |
| [Us] Rated Supply Voltage | 100240 V AC |
| Discrete Input Number | 24, discrete input 8 fast input IEC 61131-2 Type 1 |
| Discrete Output Type | Relay Transistor |
| Discrete Output Number | 4 transistor 4 fast output 12 relay |
| Discrete Output Voltage | 5125 V DC relay output 5250 V AC relay output 24 V DC transistor output |
| Discrete Output Current | 0.1 A fast output (PTO mode) TR0TR3) 2 A relay output Q4Q15) 0.5 A transistor output TR0TR3) |

Complementary

| Discrete I/O Number | 40 |
|---|---|
| Maximum Number Of I/O Expansion Module | 7 (local I/O-Architecture) 14 (remote I/O-Architecture) |
| Supply Voltage Limits | 85264 V |
| Network Frequency | 50/60 Hz |
| Discrete Input Logic | Sink or source |
| Discrete Input Voltage | 24 V |
| Discrete Input Voltage Type | DC |
| Voltage State 1 Guaranteed | >= 15 V input |
| Voltage State 0 Guaranteed | <= 5 V input |
| Discrete Input Current | 7 mA input |
| Input Impedance | 4.7 kOhm input |
| Response Time | 50 μs turn-on, I0I15 input |
| Configurable Filtering Time | 1 µs fast input |
| Discrete Output Logic | Positive logic (source) |
| Output Voltage Limits | 125 V DC relay output 30 V DC transistor output 277 V AC relay output |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Maximum Output Frequency | 1 kHz transistor output |
|-----------------------------------|--|
| | 20 kHz fast output (PWM mode) |
| | 100 kHz fast output (PLS mode) |
| Accuracy | +/- 0.1 % 0.020.1 kHz fast output |
| | +/- 1 % 0.11 kHz fast output |
| Protection Type | Short-circuit protection transistor output |
| | Short-circuit and overload protection with automatic reset transistor output |
| | Reverse polarity protection transistor output |
| | Without protection relay output |
| Reset Time | 10 ms automatic reset output |
| | 12 s automatic reset fast output |
| Memory Capacity | 64 MB system memory RAM |
| Data Backed Up | 128 MB built-in flash memory backup of user programs |
| Data Storage Equipment | <= 16 GB SD card optional) |
| Battery Type | BR2032 lithium non-rechargeable 4 year(s) |
| Backup Time | 2 years 77 °F (25 °C) |
| Execution Time For 1 Kinstruction | 0.3 ms event and periodic task |
| | 0.7 ms other instruction |
| Application Structure | 4 cyclic master tasks |
| | 8 event tasks |
| | 8 external event tasks |
| | 3 cyclic master tasks + 1 freewheeling task |
| Realtime Clock | With |
| Clock Drift | <= 60 s/month 77 °F (25 °C) |
| Positioning Functions | PTO 4 100 kHz) |
| Counting Input Number | 4 fast input (HSC mode) 200 kHz |
| | 14 standard input 1 kHz |
| Control Signal Type | A/B 100 kHz fast input (HSC mode) |
| | Pulse/direction 200 kHz fast input (HSC mode) |
| | Single phase 200 kHz fast input (HSC mode) |
| Integrated Connection Type | Non isolated serial link serial 1 RJ45 RS232/RS485 |
| | Non isolated serial link serial 2 removable screw terminal block RS485 |
| | USB port mini B USB 2.0 |
| | Ethernet RJ45 |
| Supply | Serial 1)serial link supply 5 V, <200 mA |
| Transmission Rate | 1.2115.2 kbit/s (115.2 kbit/s by default) 49.21 ft (15 m) RS485 |
| | 1.2115.2 kbit/s (115.2 kbit/s by default) 9.84 ft (3 m) RS232 |
| | 480 Mbit/s 9.84 ft (3 m) USB 10/100 Mbit/s Ethernet |
| | |
| Communication Port Protocol | Non isolated serial link Modbus master/slave |
| Port Ethernet | 10BASE-T/100BASE-TX - 1 copper cable |

| Ethernet Services | FDR DHCP server via TM4 Ethernet switch network module DHCP client embedded Ethernet port SMS notifications Updating firmware SNMP client/server Programming NGVL Monitoring IEC VAR ACCESS FTP client/server Downloading SQL client |
|---|---|
| | Modbus TCP client I/O scanner Ethernet/IP originator I/O scanner embedded Ethernet port Ethernet/IP target, Modbus TCP server and Modbus TCP slave Send and receive email from the controller based on TCP/UDP library Web server (WebVisu & XWeb system) OPC UA server DNS client |
| Local Signalling | for PWR 1 LED (green) for RUN 1 LED (green) for module error (ERR) 1 LED (red) for I/O error (I/O) 1 LED (red) for SD card access (SD) 1 LED (green) for BAT 1 LED (red) for SL1 1 LED (red) for SL2 1 LED (green) for SL2 1 LED (green) for bus fault on TM4 (TM4) 1 LED (red) for I/O state 1 LED per channel (green) for Ethernet port activity 1 LED (green) |
| Electrical Connection | removable screw terminal block for inputs and outputs pitch 5.08 mm) removable screw terminal block for connecting the 24 V DC power supply pitch 5.08 mm) |
| Maximum Cable Distance Between Devices | Unshielded cable <164.04 ft (50 m) input Shielded cable <32.81 ft (10 m) fast input Unshielded cable <164.04 ft (50 m) output Shielded cable <9.84 ft (3 m) fast output |
| Insulation | Between supply and internal logic 500 V AC Non-insulated between supply and ground |
| Marking | CE |
| Sensor Power Supply | 24 V DC 400 mA supplied by the controller |
| Surge Withstand | 2 kV power lines (AC) common mode IEC 61000-4-5 2 kV relay output common mode IEC 61000-4-5 1 kV shielded cable common mode IEC 61000-4-5 1 kV power lines (AC) differential mode IEC 61000-4-5 1 kV relay output differential mode IEC 61000-4-5 1 kV input common mode IEC 61000-4-5 1 kV transistor output common mode IEC 61000-4-5 |
| Web Services | Web server |
| Maximum Number Of Connections | 8 Modbus server 8 SoMachine protocol 10 web server 4 FTP server 16 Ethernet/IP target 8 Modbus client |
| Number Of Server Device(S) | 64 Modbus TCP 16 EtherNet/IP |
| Cycle Time | 10 ms 16 EtherNet/IP 64 ms 64 Modbus TCP |
| Mounting Support | Top hat type TH35-15 rail IEC 60715 Top hat type TH35-7.5 rail IEC 60715 plate or panel with fixing kit |
| Height | 3.54 in (90 mm) |
| Depth | 3.74 in (95 mm) |

7.48 in (190 mm)

Net Weight

1.37 lb(US) (0.62 kg)

Environment

| LINIOIIIIeilt | |
|--|--|
| Standards | ANSI/ISA 12-12-01 |
| | CSA C22.2 No 142 |
| | CSA C22.2 No 213 |
| | IEC 61131-2:2007 |
| | Marine specification (LR, ABS, DNV, GL) |
| | UL 508 |
| Product Certifications | RCM |
| | cULus |
| | CE |
| | UKCA |
| | DNV-GL |
| | ABS |
| | LR |
| Resistance To Electrostatic | 8 kV in air IEC 61000-4-2 |
| Discharge | 4 kV on contact IEC 61000-4-2 |
| Resistance To Electromagnetic | 9.14 V/m (10 V/m) 80 MHz1 GHz IEC 61000-4-3 |
| Fields | 2.74 V/m (3 V/m) 1.4 GHz2 GHz IEC 61000-4-3 |
| | 0.91 V/m (1 V/m) 2 GHz3 GHz IEC 61000-4-3 |
| Resistance To Fast Transients | 2 kV IEC 61000-4-4 power lines) |
| | 2 kV IEC 61000-4-4 relay output) |
| | 1 kV IEC 61000-4-4 Ethernet line) |
| | 1 kV IEC 61000-4-4 serial link) |
| | 1 kV IEC 61000-4-4 input) |
| | 1 kV IEC 61000-4-4 transistor output) |
| Resistance To Conducted | 10 V 0.1580 MHz IEC 61000-4-6 |
| Disturbances | 3 V 0.180 MHz Marine specification (LR, ABS, DNV, GL) |
| | 10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) Marine |
| | specification (LR, ABS, DNV, GL) |
| Electromagnetic Emission | Conducted emissions 12069 dBµV/m QP power lines)10150 kHz IEC 55011 |
| 6 | Conducted emissions 63 dBµV/m QP power lines)1.530 MHz IEC 55011 |
| | Conducted emissions 79 dBµV/m QP/66 dBµV/m AV power lines)0.150.5 MHz IEC |
| | 55011 |
| | Conducted emissions 73 dBµV/m QP/60 dBµV/m AV power lines)0.5…300 MHz IEC |
| | 55011 |
| | Radiated emissions 40 dBµV/m QP class A 10 m)30230 MHz IEC 55011 |
| | Conducted emissions 7963 dBµV/m QP power lines)1501500 kHz IEC 55011 |
| | Radiated emissions 47 dBµV/m QP class A 10 m)230…1000 MHz IEC 55011 |
| Immunity To Microbreaks | 10 ms |
| Ambient Air Temperature For | 14122 °F (-1050 °C) vertical installation) |
| Operation | 14131 °F (-1055 °C) horizontal installation) |
| Ambient Air Temperature For Storage | -13158 °F (-2570 °C) |
| Relative Humidity | 1095 %, without condensation in operation) |
| | 1095 %, without condensation in storage) |
| Ip Degree Of Protection | IP20 with protective cover in place |
| Pollution Degree | 2 |
| Operating Altitude | 0.6561.68.ft (0.2000 m) |
| | 06561.68 ft (02000 m) |
| Storage Altitude | 0.009842.52 ft (03000 m) |
| Vibration Resistance | 3.5 mm 58.4 Hz symmetrical rail |
| | 3 gn 8.4150 Hz symmetrical rail |
| | 3.5 mm 58.4 Hz panel mounting |
| | 3 gn 8.4150 Hz panel mounting |
| Shock Resistance | 15 gn 11 ms |
| | |

Ordering and shipping details

| Category | US10MSX22533 | |
|-------------------|---------------|--|
| Discount Schedule | OMSX | |
| Gtin | 3606480648847 | |
| Returnability | Yes | |
| Country Of Origin | ID | |

Packing Units

| • | |
|------------------------------|-------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.04 in (12.8 cm) |
| Package 1 Width | 8.90 in (22.6 cm) |
| Package 1 Length | 4.53 in (11.5 cm) |
| Package 1 Weight | 32.91 oz (933.0 g) |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 6 |
| Package 2 Height | 11.81 in (30 cm) |
| Package 2 Width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Package 2 Weight | 12.85 lb(US) (5.827 kg) |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 48 |
| Package 3 Height | 29.53 in (75.0 cm) |
| Package 3 Width | 15.75 in (40.0 cm) |
| Package 3 Length | 31.50 in (80.0 cm) |
| Package 3 Weight | 132.28 lb(US) (60 kg) |
| | |

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings


Dimensions







Mounting and Clearance

Clearance






Mounting Position




Acceptable Mounting



NOTE: Expansion modules must be mounted above the logic controller.


Incorrect Mounting



Apr 19, 2024

Direct Mounting On a Panel Surface


Mounting Hole Layout



Connections and Schema


Digital Inputs

Wiring Diagram (Positive Logic)



- (*): Type T fuse
- (1): The COM0, COM1 and COM2 terminals are not connected internally.


Wiring Diagram (Negative Logic)



- (*): Type T fuse
- (1): The COM0, COM1 and COM2 terminals are not connected internally.

Fast Transistor Outputs


Wiring Diagram



(*): 2 A fast-blow fuse

Relay Outputs

Wiring Diagram




(*): Type T fuse

(1): The terminals COM1 to COM6 are not connected internally.

(2): To improve the life time of the contacts, and to protect from potential inductive load damage, you must connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load

USB Mini-B Connection



Ethernet Connection to a PC

