

Product data sheet

Specifications



spring return contact block - 3 NC - base mounting

XACS3991

⚠ Discontinued on: Mar 31, 2022

⚠ Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Isolating block
Component Name	XACS
Electrical Circuit Type	Power circuit
Contact Block Application	Emergency stop push-button
Contact Block Type	Single
Type Of Operator	Spring return
Product Compatibility	ZA2BS14 head XACB
Mechanical Interlocking	Without mechanical interlock
Contacts Type And Composition	3 NC
Mounting Of Block	Base mounting
Contact Operation	Snap action

Complementary

Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Mechanical Durability	1000000 cycles
Contact Code Designation	A300 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A Q300 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A
[Ui] Rated Insulation Voltage	400 V 3)IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Rated Operational Power In W	3000 W AC-23B 400 V
Terminals Description Iso N°1	(31-32)NC (21-22)NC (11-12)NC
Terminal Identifier	(13-14)NO (11-12)NC
Net Weight	0.24 lb(US) (0.11 kg)

Environment

Standards	EN 60947-3 IEC 60947-3 CSA C22.2 No 14
-----------	--

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140

Ordering and shipping details

Category	22473-PUSHBUTTON, PENDANTS
Discount Schedule	CS2
Gtin	3389110647464
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov