Product data sheet

Specifications





Compact I/O expansion block, Modicon TM5, 8 AI, 8 AO, 0 10 V -12 bits

TM5CAI8O8VL

! Discontinued on: Dec 2, 2020

! To be end-of-service on: Sep 1, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon TM5		
Product Or Component Type	Compact I/O expansion block		
Enclosure Material	Plastic		
Color	White		
Input/Output Number	16		
Input/Output Number Of Splitter Box	81+80		
Number Of Modules	Analog input 2 x 4 Analog output 2 x 4		
Analogue Input Number	8		
Analogue Input Range	+/- 10 V		
Analogue Input Resolution	12 bits voltage		
Analogue Output Number	8		
Analogue Output Type	Voltage 8		
Analogue Output Range	+/- 10 V		

Complementary

Input Filtering	<= 50 ms not configurable		
Sampling Duration	20 ms input/output for the whole module 5 ms input/output per channel		
Response Time	<= 1 ms status change output		
Maximum Leakage Current	5 μA when switched off) output		
Protection Type	Short-circuit output		
Isolation	No insulation between channels 500 Vrms AC insulation between channel and bus		
Current Consumption	8 mA 5 V DC bus 218 mA 24 V DC input/output		
Power Dissipation In W 5.25 W			
Local Signalling	for power supply 4 LEDs (green) for power supply 4 LEDs (red) for output status 8 LEDs (yellow) for input status 8 LEDs (green)		
Electrical Connection	n Removable spring terminal block		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Surge Withstand	0.5 kV differential mode 24 V DC EN/IEC 61000-4-5 1 kV common mode 24 V DC EN/IEC 61000-4-5		
Mounting Support	DIN rail		
Net Weight	0.55 lb(US) (0.25 kg)		

Environment

Environment				
Standards	UL 508 CSA C22.2 No 142 CSA C22.2 No 213 IEC 61131-2			
Product Certifications	C-tick GOST-R UL CSA			
Marking	CE			
Ambient Air Temperature For Operation	14122 °F (-1050 °C) vertical installation) 14140 °F (-1060 °C) horizontal installation)			
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)			
Relative Humidity	595 % without condensation			
Ip Degree Of Protection	IP20IEC 61131-2			
Pollution Degree	2 IEC 60664			
Operating Altitude	06561.68 ft (02000 m)			
Storage Altitude	0.009842.52 ft (03000 m)			
Vibration Resistance	1 gn 8.4150 Hz DIN rail 3.5 mm 58.4 Hz DIN rail			
Shock Resistance	15 gn 11 ms			
Resistance To Electrostatic 4 kV on contact EN/IEC 61000-4-2 Discharge 8 kV in air EN/IEC 61000-4-2				
Resistance To Electromagnetic Fields	0.91 V/m (1 V/m) 22.7 GHz EN/IEC 61000-4-3 9.14 V/m (10 V/m) 802000 MHz EN/IEC 61000-4-3			
Resistance To Fast Transients	1 kV EN/IEC 61000-4-4 I/O) 1 kV EN/IEC 61000-4-4 shielded cable) 2 kV EN/IEC 61000-4-4 power lines)			
Electromagnetic Compatibility	EN/IEC 61000-4-6			
Disturbance Radiated/Conducted	CISPR 11 zone B - class A			

Ordering and shipping details

Category	US1PC1222532	
Discount Schedule	PC12	
Gtin	3595864145129	
Returnability	No	
Country Of Origin	AT	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	3.54 in (9.0 cm)

Package 1 Length	4.33 in (11.0 cm)	
Package 1 Weight	10.02 oz (284.0 g)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	36	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	22.54 lb(US) (10.224 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free
⊘	Mercury Free
Ø	Rohs Exemption Information Yes
②	Pvc Free

Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	End of Life Information			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

Product data sheet

TM5CAI8O8VL

Presentation

TM5 Compact I/O Module




N°	Designation
1	Analog Input electronic module / 4 Analog Inputs
2	Dummy Module
3	Analog Output electronic module / 4 Analog Outputs


TM5CAI8O8VL

Dimensions Drawings

Compact I/O Module

Dimensions







TM5CAI8O8VL

Mounting and Clearance


TM5 System


Spacing Requirements






Mounting on a DIN Rail







Product data sheet

TM5CAI8O8VL

Connections and Schema


TM5 System Wiring Recommendations

Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	0.35		Ω		
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

Analog Input 4AI ±10 V


Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- **U** Voltage

Analog Output 4AO ±10 V

Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- **U** Voltage