

Product data sheet

Specifications



empty control station - XAP-A - plastic - without opening - H2

XAPA4100H2

⚠ Discontinued on: Jan 29, 2021

⚠ Discontinued

Main

Range Of Product	Harmony XAP
Product Or Component Type	Empty control station without hinges
Device Short Name	XAPA
Product Front Plate Size	151 x 241 mm
Usable Depth	3.27 in (83 mm)
Number Of Cut-Out	Undrilled
Colour Of Base Of Enclosure	Grey
Colour Of Cover	Grey
Material	Glass reinforced polyester
Cable Entry	Undrilled
Device Mounting	Flush
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water

Complementary

Net Weight	1.96 lb(US) (0.89 kg)
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94

Environment

Protective Treatment	TC TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-40...158 °F (-40...70 °C)
Overvoltage Category	Class II IEC 60536 Class II NF C 20-030
Fire Resistance	1562 °F (850 °C) NF C 20-455 1760 °F (960 °C) IEC 92

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389119414456
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.12 in (13 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	9.84 in (25 cm)
Package 1 Weight	2.31 lb(US) (1.05 kg)

Contractual warranty

Warranty	18 months
----------	-----------