Product data sheet

Specifications





Die cast empty control station, Harmony XAP, zinc alloy, grey, 3 cut outs, 22mm, 130x80x51.5mm

XAPG29703

Product availability: Stock - Normally stocked in distribution facility

Price*: 213.00 USD

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPG	
Product Destination	For Ø 22 mm control and signalling units	
Number Of Cut-Out	3 cut-outs	
Colour Of Base Of Enclosure	Grey RAL 7032)	
Colour Of Cover	Grey RAL 7032)	
Control Station Type	Metal	
Material	Die cast zinc	
Sale Per Indivisible Quantity	1	
Ip Degree Of Protection	IP65 IEC 60529 IP657 IEC 60529	
Resistance To Chemical Agents	Special treatment can be obtained on request	

Complementary

Number Of Vertical Rows	1
Number Of Horizontal Rows	3
Cut-Out Dimensions	Ø 22 mm
Cable Entry	cable gland 1 x cable gland
Thread Type	3/4 NPT
Cad Overall Width	3.15 in (80 mm)
Cad Overall Height	5.12 in (130 mm)
Cad Overall Depth	2.03 in (51.5 mm)
Net Weight	1.33 lb(US) (0.605 kg)
Compatibility Code	XAPG

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030
Ik Degree Of Protection	IK07 IEC 62262

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389118381810
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	3.50 in (8.9 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	24.23 oz (687 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	19.36 lb(US) (8.783 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov