

Product data sheet


Characteristics

TSXDEZ32D2

TSX Micro - 32 Discret Input DC

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 993.00 USD



Main

Range of product	Modicon TSX Micro automation platform
Product or component type	Discrete input module
Discrete input number	32 screw terminal block
Discrete input voltage	24 V DC positive or negative 19...30 V
Discrete input current	7 mA
Input voltage limits	≥ 11 V at state 1 < 5 V at state 0
Current state 0 guaranteed	≤ 2 mA
Current state 1 guaranteed	≥ 6 mA
Input impedance	3.4 Ohm
Response time	0.1...7.5 ms at state 0 to state 1 0.1...7.5 ms at state 1 to state 0

Complementary

Standards	IEC 1131-2 Type 2
Input compatibility	2/3-wire proximity sensors PNP/NPN
Discrete input type	Current sink
Current consumption	254 mA positive
Isolation voltage	1500 V AC 1 s

Ordering and shipping details

Category	22556 - TSX MICRO, PL7 MICRO & ACCESS
Discount Schedule	PC14
GTIN	00785901871095
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	N
Country of origin	FR

Offer Sustainability


RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Sensors/Inputs Connections

Wiring Diagram



FU1 and FU2 = 0.5A rapid fusion fuses.