Product data sheet

Specifications





Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, 1 cut-out, Ø22, with ISO cable entries, 80 x 80 x 51.5 mm

XAPM1201H29

① Discontinued

! Discontinued on: Aug 30, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP
Product Or Component Type	Die-cast empty control station
Device Short Name	XAPM
Product Destination	For Ø 22 mm control and signalling units
Product Front Plate Size	80 x 80 mm
Usable Depth	1.93 in (49 mm)
Number Of Cut-Out	1 cut-out
Colour Of Base Of Enclosure	Blue
Colour Of Cover	Blue
Material	Zinc alloy
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland 0.79 in (20 mm) 1 hole without blanking plug for ISO 429248 cable gland 0.79 in (20 mm)
Device Mounting	Flush
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K

Complementary

Number Of Vertical Rows	1
Net Weight	1.00 lb(US) (0.455 kg)

Environment

Protective Treatment	TC				
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)				
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)				
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030				

Ordering and shipping details

Category	US10CS222466				
Discount Schedule	0CS2				

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3389110312621
Returnability	No
Country Of Origin	MA

Packing Units

Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	3.23 in (8.2 cm)				
Package 1 Width	3.54 in (9 cm)				
Package 1 Length	3.62 in (9.2 cm)				
Package 1 Weight	18.48 oz (524 g)				

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
	Mercury Free	
Ø	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Dimensions and Fixing

Refer to the product characteristics to get the number of cut-outs.



- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.

P Usable depth

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	80	3.15	51.5	2.01	50	1.97	65	2.56	49	1.93