Product data sheet

Specifications

≺Green Premium"



empty control station - XAP-M - zinc alloy - without opening

XAPM21H29

- () Discontinued on: Jun 30, 2022
- (!) End-of-service on: Jul 28, 2022

Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	ХАРМ						
Product Front Plate Size	80 x 130 mm						
Usable Depth	1.93 in (49 mm)						
Number Of Cut-Out	Undrilled						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Blue						
Material	Zinc alloy						
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland 0.79 in (20 mm) 1 hole without blanking plug for ISO 429248 cable gland 0.79 in (20 mm)						
Product Mounting	Flush mounting						
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K						

Complementary

Electrical Shock Protection Class

Net Weight	1.37 lb(US) (0.62 kg)				
Environment					
Protective Treatment	TC				
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)				
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)				

Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389118115552
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.78 in (9.6 cm)
Package 1 Width	3.46 in (8.8 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	25.11 oz (712 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity

а		b		с		G		н		P	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	130	5.12	51.5	2.03	50	1.97	115	4.53	49	1.93

(3) 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.