Product data sheet





Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, 3 cut-outs, Ø22, with ISO cable entries, 80 x 130 x 51.5 mm

XAPM2203H29

(!) Discontinued on: Jun 17, 2022



Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	XAPM					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	80 x 130 mm					
Usable Depth	1.93 in (49 mm)					
Number Of Cut-Out	3 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland 0.79 in (20 mm) 1 hole without blanking plug for ISO 429248 cable gland 0.79 in (20 mm)					
Device Mounting	Flush					
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K					

Complementary

Number Of Vertical Rows	1
Net Weight	1.33 lb(US) (0.605 kg)

Environment

Protective Treatment	TC					
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)					
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)					
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030					

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)		
Discount Schedule	CS2		
Gtin	3389110312683		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability No

Packing Units

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	3.62 in (9.2 cm)			
Package 1 Width	4.49 in (11.4 cm)			
Package 1 Length	7.17 in (18.2 cm)			
Package 1 Weight	24.83 oz (704 g)			

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
- P Usable depth

а		b		С		G		Н		P	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	130	5.12	51.5	2.03	50	1.97	115	4.53	49	1.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



b1 Vertical interaxis: 30 mm/1.18 in.