Product data sheet

Specifications





(!) Discontinued

Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, 6 cut-outs, Ø22, with ISO cable entries, 80 x 220 x 77 mm

XAPM4506H29

- Discontinued on: Jun 30, 2022
- ! End-of-service on: Jul 28, 2022

Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	XAPM						
Product Destination	For Ø 22 mm control and signalling units						
Product Front Plate Size	80 x 220 mm						
Usable Depth	2.93 in (74.5 mm)						
Number Of Cut-Out	6 cut-outs						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Blue						
Material	Zinc alloy						
Cable Entry	1 hole without blanking plug for ISO 429248 cable gland 0.98 in (25 mm)						
Device Mounting	Flush						
Ip Degree Of Protection	IP65 IEC 60529						

Complementary

Number Of Vertical Rows	1
Net Weight	3.04 lb(US) (1.38 kg)

Environment

Protective Treatment	TC -40158 °F (-4070 °C)				
Ambient Air Temperature For Storage					
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)				
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030				

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389118115347

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	3.39 in (8.6 cm)			
Package 1 Width	5.20 in (13.2 cm)			
Package 1 Length	9.06 in (23 cm)			
Package 1 Weight	3.43 lb(US) (1.556 kg)			

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Dimensions and Fixing



- 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity (1)
- 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in. (3)
- Usable depth

а		b		C .		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	220	6.89	77	3.03	50	1.97	205	8.07	74.5	2.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



Vertical interaxis: 30 mm/1.18 in.