Product data sheet

Specification





Switch disconnector, TeSys Control, for ON/emergency stop, 20A(V01), Ã~22.5 fixing, for mounting at back of an enclosure

VCCD01

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 185.00 USD

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCCD
Product Type	Emergency stop switch disconnector

Complementary

Switch
Shaft extension
Handle
Handle door
Switch symmetrical rail
Switch plate
Hole 0.89 in (22.5 mm) handle
By clips switch
By screws switch
High performance
3P
3 NO
690 V AC 50/60 Hz
11 kW 690 V AC-23A)
3 kW 230240 V AC-3)
4 kW 400415 V AC-3)
5.5 kW 500 V AC-3)
7.5 kW 500 V AC-23A)
7.5 kW 690 V AC-3)
4 kW 230240 V AC-23A)
5.5 kW 400415 V AC-23A)
11 A AC-23 Ue: 400 V
20 A
16 A
200 A 400 V AC-21A
200 A 400 V AC-22A
200 A 400 V AC-23A
200 A 400 V AC-21A)
200 A 400 V AC-22A)
200 A 400 V AC-23A)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Rated Conditional Short Circuit Current	10 kA 400 V 20 A aM 10 kA 400 V 20 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	300 A 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability For Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Extended
Handle Color	Red
Handle Front Plate Color	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 0.160.31 in (48 mm)
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-15
lec Terminal Connection	Power circuit screw clamp terminals 0.02 in² (10 mm²) solid Power circuit screw clamp terminals 0.01 in² (6 mm²) flexible - with cable end
Tightening Torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Base Dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Product Weight	0.86 lb(US) (0.392 kg)

Environment

Standards	IEC 60947-3
Product Certifications	CCC CSA GL UL UKCA
Degree Of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	тс
Mechanical Robustness	Vibrations 10150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature For Operation	-4122 °F (-2050 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	Main switch disconnector

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1

Gtin	3389110759785
Returnability	No
Country Of Origin	C7

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.03 in (7.700 cm)
Package 1 Width	3.50 in (8.900 cm)
Package 1 Length	10.04 in (25.500 cm)
Package 1 Weight	12.45 oz (353.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	12.73 lb(US) (5.773 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free
②	Mercury Free
⊘	Rohs Exemption Information Yes
②	Pvc Free
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov