Product data sheet

Specification





Harmony, 22mm Push Button, 2 position selector switch, black, maintained, 1 NO, 600 V

XB4BD21

Product availability: Stock - Normally stocked in distribution facility

Price*: 51.00 USD

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Selector switch	
Device Short Name	XB4	
Bezel Material	Chromium plated metal	
Fixing Collar Material	Zamak	
Mounting Diameter	0.89 in (22.5 mm)	
Sale Per Indivisible Quantity	1	
Head Type	Standard	
Shape Of Signaling Unit Head	Round	
Type Of Operator	stay put	
Operator Profile	Black standard handle	
Operator Position Information	2 positions 90°	
Contacts Type And Composition	1 NO	
Contact Operation	Slow-break	
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end IEC 60947-1 Screw clamp terminals, >= 1 x 0.22 mm² without cable end IEC 60947-1	

Complementary

Height	1.85 in (47 mm)	
Width	1.18 in (30 mm)	
Depth	2.68 in (68 mm)	
Terminals Description Iso N°1	(13-14)NO	
Net Weight	0.21 lb(US) (0.095 kg)	
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
Contacts Usage	Standard contacts	
Positive Opening	Without	
Torque Value	1.24 lbf.in (0.14 N.m) NO changing electrical state	
Mechanical Durability	1000000 cycles	
Tightening Torque	7.0810.62 lbf.in (0.81.2 N.m) IEC 60947-1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shape Of Screw Head	Cross Philips no 1
	Cross pozidriv No 1
	Slotted flat Ø 4 mm
	Slotted flat Ø 5.5 mm
Contacts Material	Silver alloy (Ag/Ni)
Short-Circuit Protection	10 A cartridge fuse gG IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A IEC 60947-5-1
[Ui] Rated Insulation Voltage	600 V 3)IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
[le] Rated Operational Current	3 A 240 V, AC-15, A600 IEC 60947-5-1
	6 A 120 V, AC-15, A600 IEC 60947-5-1
	0.1 A 600 V, DC-13, Q600 IEC 60947-5-1
	0.27 A 250 V, DC-13, Q600 IEC 60947-5-1
	0.55 A 125 V, DC-13, Q600 IEC 60947-5-1
	1.2 A 600 V, AC-15, A600 IEC 60947-5-1
Electrical Durability	1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C
-	1000000 cycles, AC-15, 3 A 120 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C
	1000000 cycles, AC-15, 4 A 24 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C
	1000000 cycles, DC-13, 0.2 A 110 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C
	1000000 cycles, DC-13, 0.5 A 24 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C
Electrical Reliability	Λ < 10exp(-6) 5 V 1 mA in clean environment IEC 60947-5-4
	Λ < 10exp(-8) 17 V 5 mA in clean environment IEC 60947-5-4
Device Presentation	Complete product
Environment	
Protective Treatment	TH

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class I IEC 60536
Ip Degree Of Protection	IP69 IP69K IP67 IEC 60529
Nema Degree Of Protection	NEMA 13 NEMA 4X
Standards	CSA C22.2 No 14 IEC 60947-5-1 JIS C8201-5-1 IEC 60947-1 IEC 60947-5-4 IEC 60947-5-5 UL 508 JIS C8201-1
Product Certifications	LROS (Lloyds register of shipping) BV UL GL CSA DNV
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	US10CS222468
Discount Schedule	0CS2

Gtin	3389110887075
Returnability	Yes
Country Of Origin	US

Packing Units

PCE
1
1.46 in (3.700 cm)
2.17 in (5.500 cm)
3.58 in (9.100 cm)
3.35 oz (95.000 g)
BB1
5
3.54 in (9.000 cm)
1.34 in (3.400 cm)
10.43 in (26.500 cm)
16.79 oz (476.000 g)
S03
100
11.81 in (30.000 cm)
11.81 in (30.000 cm)
15.75 in (40.000 cm)
22.17 lb(US) (10.055 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions



e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

XB4BD21


Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connectors or on Printed Circuit Board

(1)

Connection by Screw Clamp Terminals or Plug-in



(6)

(4)

Connection by Faston Connectors

(1) Diameter on finished panel or support

(3)

- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0^{+0.4}$ / 0.88 in. $_0^{+0.016}$)

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.