

Product data sheet

Specifications



Empty pendant control station,
Harmony XAC, plastic,yellow, 12 cut
outs, for cable 10...22mm

XACB1215

Product availability: Non-Stock - Not normally stocked in
distribution facility

❗ Discontinued

Main

| | |
|---------------------------|-------------------------|
| Range Of Product | Harmony XAC |
| Product Or Component Type | Pendant control station |
| Device Short Name | XACB |

Complementary

| | |
|---------------------------------------|--|
| Control Station Type | Double insulated |
| Enclosure Material | Glass reinforced polyester |
| Electrical Circuit Type | Power circuit Control circuit |
| Enclosure Type | Empty enclosure |
| Number Of Cut-Out | 12 cut-outs in 2 rows |
| Control Station Colour | Yellow |
| Cable Entry | Rubber sleeve with stepped entry 0.87...1.38 in (22...35 mm) |
| Guard Rail | Without |
| Vertical Operator Cut-Out Centre | 1.57 in (40 mm) |
| Standards | IEC 60947-5-1 CSA C22.2 No 14 |
| Product Certifications | CSA type 4 |
| Protective Treatment | TH |
| Ambient Air Temperature For Operation | -13...158 °F (-25...70 °C) |
| Ambient Air Temperature For Storage | -40...158 °F (-40...70 °C) |
| Vibration Resistance | 15 gn 10...500 Hz)IEC 60068-2-6 |
| Shock Resistance | 100 gn IEC 60068-2-27 |
| Overvoltage Category | Class II IEC 61140 |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Mechanical Durability | 1000000 cycles |
| Net Weight | 3.66 lb(US) (1.66 kg) |

Ordering and shipping details

| | |
|----------|--------------|
| Category | US10CS222473 |
|----------|--------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|---------------|
| Discount Schedule | 0CS2 |
| Gtin | 3389110665611 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.74 in (9.500 cm) |
| Package 1 Width | 25.98 in (66.000 cm) |
| Package 1 Length | 6.30 in (16.000 cm) |
| Package 1 Weight | 3.97 lb(US) (1.800 kg) |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 15 |
| Package 2 Height | 29.53 in (75.000 cm) |
| Package 2 Width | 23.62 in (60.000 cm) |
| Package 2 Length | 31.50 in (80.000 cm) |
| Package 2 Weight | 88.18 lb(US) (40.000 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)


Well-being performance

| | | |
|---|----------------------------|--|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration |
| | | |
| Weee | | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| | | |
| California Proposition 65 | | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Dimensions

Below drawing shows a product with 12 cut-outs. Select the number of cut-outs according to the product characteristics in order to get b, b1 and c dimensions.




Dimensions in mm

| Number of cut-outs | 2 | 4 | 6 | 8 | 12 |
|--------------------|-----|-----|-----|-----|-----|
| b | 409 | 499 | 589 | 679 | 593 |
| b1 | 220 | 310 | 400 | 490 | 404 |
| c | 98 | 98 | 98 | 98 | 158 |
| d | 40 | 40 | 40 | 40 | 40 |

Dimensions in in.

| Number of cut-outs | 2 | 4 | 6 | 8 | 12 |
|--------------------|-------|-------|-------|-------|-------|
| b | 16.10 | 19.64 | 23.19 | 26.73 | 23.35 |
| b1 | 8.66 | 12.20 | 15.75 | 19.29 | 15.90 |
| c | 3.86 | 3.86 | 3.86 | 3.86 | 6.22 |
| d | 1.57 | 1.57 | 1.57 | 1.57 | 1.57 |

Protective cable sleeves




(1) Internal ø

Connections and Schema


Control of Single-Speed Reversing Motor

With XESD1181 contact block, to be ordered separately



Control of 2-Speed Reversing Motor


With XESD1281 contact block, to be ordered separately




KM High speed contactor

Control of Single-Speed Reversing Motor 2-Phase Switching

With XESD1191 contact block, to be ordered separately




Combined with 3-pole isolating block XACS399 or XACS3991, shown in the unoperated position (pendant station “supplied”), fitted with key release trigger action latching Emergency stop operator.




Control of 2-Speed Reversing Motor 2-Phase Switching

With XESD1291 contact block, to be ordered separately



Control of Single-Speed Reversing Motor 3-Phase switching, Reversing by 2-Phase Inversion

With XESD2201 contact block, to be ordered separately



Control of Single-Speed Reversing Motor 3-Phase switching, Reversing by 2-Phase Inversion

With XESD2241 contact block, to be ordered separately

