


Product data sheet

Specifications



pendant control station XAC-B - 2 pushbuttons - 2.2 kW - 380 V

XACB291

 **Discontinued on:** Oct 20, 2020

 **Discontinued**

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACB

Complementary

Control Station Type	Double insulated
Enclosure Material	Glass reinforced polyester
Electrical Circuit Type	Power circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of single speed hoist motor
Control Station Composition	2 push-buttons
Control Button Type	Second push-button 2-pole lower, slow First push-button 1 NO + 1 NO 2-pole raise, slow
Product Compatibility	XESD1191 for reversing operation
Mechanical Interlocking	With mechanical interlocking
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32
Product Certifications	CCC GOST
Protective Treatment	TH
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102
Mechanical Durability	1000000 cycles

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Cable Entry	Rubber sleeve with stepped entry 0.39...0.87 in (10...22 mm)
[Ithe] Conventional Enclosed Thermal Current	12 A
[Ui] Rated Insulation Voltage	600 V 3)
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Contact Operation	Snap action
Operating Force	17 N push-button
Short-Circuit Protection	10 A fuse protection cartridge aM
Rated Power In Hp	2 hp 240 V, CSA 3 hp 600 V, CSA 5 hp 400 V, CSA
Rated Operational Power In W	2200 W AC-3 240 V IEC 60947-3 appendix A 2200 W AC-3 400 V IEC 60947-3 appendix A 2200 W AC-4 240 V IEC 60947-3 appendix A 2200 W AC-4 400 V IEC 60947-3 appendix A
Electrical Durability	300000 cycles AC-3, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-3, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-3, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-4, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-3, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-4, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminals Description Iso N°1	(23-24)NO (43-44)NO (33-34)NO (13-14)NO
Terminals Description Iso N°2	(31-32)NC (11-12)NC (21-22)NC
Terminal Identifier	(11-12)NC (13-14)NO
Net Weight	1.87 lb(US) (0.85 kg)

Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
Gtin	3389110641745
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10 cm)
Package 1 Width	4.33 in (11 cm)
Package 1 Length	20.47 in (52 cm)
Package 1 Weight	2.21 lb(US) (1.004 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65		WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov