

Product data sheet

Specifications



pendant control station XAC-B - 6 pushbuttons 1 Emergency stop

XACB6911

⚠ Discontinued on: Mar 31, 2020

⚠ Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACB

Complementary

Control Station Type	Double insulated
Enclosure Material	Glass reinforced polyester
Electrical Circuit Type	Power circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of single speed hoist motor
Control Station Composition	6 push-buttons + 1 emergency stop
Control Button Type	Stop push-button Ø 40 mm 3 NC latching First push-button 2-pole raise, slow Second push-button 2-pole lower, slow Fourth push-button 2-pole left, slow Third push-button 2-pole right, slow Fifth push-button 2-pole forward slow Sixth push-button 2-pole reverse, slow
Product Compatibility	XESD1191 for reversing operation XACS3991 for emergency stop
Mechanical Interlocking	With mechanical interlocking between pairs
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60204-32
Product Certifications	CSA type 4
Protective Treatment	TH
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	1000000 cycles
Cable Entry	Rubber sleeve with stepped entry 0.39...0.87 in (10...22 mm)
[Ithe] Conventional Enclosed Thermal Current	12 A
[Ui] Rated Insulation Voltage	Emergency stop contact 400 V 3)IEC 60947-1 600 VCSA
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Contact Operation	Snap action
Operating Force	17 N push-button 40 N emergency stop
Short-Circuit Protection	10 A fuse protection cartridge aM
Rated Power In Hp	2 hp 240 V, CSA 3 hp 600 V, CSA 5 hp 400 V, CSA
Rated Operational Power In W	2200 W AC-3 240 V IEC 60947-3 appendix A 2200 W AC-3 400 V IEC 60947-3 appendix A 2200 W AC-4 240 V IEC 60947-3 appendix A 2200 W AC-4 400 V IEC 60947-3 appendix A
Electrical Durability	300000 cycles AC-3, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-3, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-3, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-4, 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-3, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-4, 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminals Description Iso N°1	(23-24)NO (43-44)NO (13-14)NO (33-34)NO
Terminals Description Iso N°2	(11-12)NC (31-32)NC (21-22)NC
Terminal Identifier	(11-12)NC (13-14)NO
Net Weight	3.31 lb(US) (1.5 kg)

Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
Gtin	3389110920116
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------