

Product data sheet

Specifications



Pendant control station, Harmony XAC, 1 speed, 1 2-directional push button, 1 emergency stop, for XEDS3111/XENT1991

XACD22P3111

! Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACD

Complementary

Control Station Type	Double insulated
Enclosure Material	Polypropylene
Control Type	Intuitive
Electrical Circuit Type	Power circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of single speed hoist motor
Motor Starter Type	Reversing
Control Station Composition	1 2-directional button + 1 emergency stop
Control Button Type	Stop push-button Ø 30 mm 3 NC latching First direction button 2-pole raise, slow Second direction button 2-pole lower, slow
Product Compatibility	XEDS3111 for reversing operation XENT1991 for emergency stop
Mechanical Interlocking	With mechanical interlocking
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Standards	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1
Protective Treatment	TH
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IK Degree Of Protection	IK08 conforming to EN 50102
Mechanical Durability	3000000 cycles
Cable Entry	Rubber sleeve with stepped entry 0.28...0.71 in (7...18 mm)
[Ithe] Conventional Enclosed Thermal Current	10 A XENT.... 16 A XEDS....
[Ui] Rated Insulation Voltage	500 V 3)IEC 60947-1 Emergency stop contact 400 V 3)
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1 4 kV emergency stop contact
Contact Operation	Snap action
Operating Force	28 N
Short-Circuit Protection	6 A fuse protection cartridge aM
Rated Operational Power In W	2200 W AC-3 400 V IEC 60947-3 appendix A 2200 W AC-4 400 V IEC 60947-3 appendix A 3000 W AC-23B 400 V
Electrical Durability	1000000 cycles AC-3, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 1000000 cycles AC-4, 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminals Description Iso N°1	(1-2)P (5-6)P (3-4)P (7-8)P
Terminals Description Iso N°2	(31-32)NC (11-12)NC (21-22)NC
Terminal Identifier	(13-14)NO (11-12)NC
Net Weight	0.90 lb(US) (0.41 kg)

Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
Gtin	3389110656107
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	4.72 in (12.0 cm)
Package 1 Length	12.60 in (32.0 cm)
Package 1 Weight	19.29 oz (547.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)

Package 2 Weight	8.73 lb(US) (3.958 kg)
------------------	------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov