## Product data sheet

Specification





# Complete push button, Harmony XB6, yellow flush pushbutton Ø 16 spring return 1NO+1NC unmarked

XB6AA55B

! Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony XB6	
Product Or Component Type	Complete push-button	
Device Short Name	XB6	
Bezel Material	Plastic	
Mounting Diameter	0.63 in (16 mm)	
Sale Per Indivisible Quantity	1	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Yellow flush, unmarked	
Contacts Type And Composition	1 NO + 1 NC	
Contact Operation	Slow-break	
Connections - Terminals	Faston connectors 2.8 x 0.5 mm	

#### Complementary

Cad Overall Width	0.71 in (18 mm)	
Cad Overall Height	0.71 in (18 mm)	
Cad Overall Depth	2.24 in (57 mm)	
Terminals Description Iso N°1	(13-14)NO (21-22)NC	
Net Weight	0.05 lb(US) (0.022 kg)	
Operating Position	Any position	
Positive Opening	With EN/IEC 60947-5-1 appendix K	
Operating Travel	0.04 in (1 mm) NO changing electrical state) 0.08 in (2 mm) NC changing electrical state) 0.14 in (3.5 mm) total travel)	
Operating Force	3.5 N NO changing electrical state 4.5 N NC changing electrical state	
Mechanical Durability	2000000 cycles	
Contacts Material	al Silver alloy (Ag/Ni)	
Short-Circuit Protection	6 A cartridge fuse gG	
[Ui] Rated Insulation Voltage	250 V 3)EN/IEC 60947-1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Uimp] Rated Impulse Withstand Voltage	4 kV EN/IEC 60947-1
[le] Rated Operational Current	3 A 120 V, AC-15, B300 EN/IEC 60947-5-1 1.5 A 240 V, AC-15, B300 EN/IEC 60947-5-1 0.1 A 250 V, DC-13, R300 EN/IEC 60947-5-1 0.22 A 125 V, DC-13, R300 EN/IEC 60947-5-1
Electrical Durability	1000000 cycles, AC-15 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C
Electrical Reliability	Λ = 10exp(-8) 5 V 1 mA with confidence level of 90 % IEC 60947-5-4

#### **Environment**

Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
<b>Electrical Shock Protection Class</b>	Class II IEC 61140	
Ip Degree Of Protection	IP65 IEC 60529	
Nema Degree Of Protection	NEMA 13 UL 50 NEMA 4 UL 50 NEMA 4X UL 50 NEMA 13 CSA C22.2 No 94 NEMA 4 CSA C22.2 No 94 NEMA 4X CSA C22.2 No 94	
Standards	EN/IEC 60947-5-5 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C 4520 UL 508 JIS C 852	
Product Certifications	CCC UL GOST CSA	
Vibration Resistance	+/- 3 mm 2500 Hz)IEC 60068-2-6 5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

## Ordering and shipping details

Category	US10CS222459	
Discount Schedule	0CS2	
Gtin	785901356172	
Returnability	No	
Country Of Origin	MX	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	3.20 oz (90.718 g)

## **Contractual warranty**

Warranty

Apr 23, 2024

18 months

### Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov