Product data sheet





Empty control station, Harmony XAP, zinc alloy, grey, undrilled, 22mm, 80x80x51.5mm

XAPG19100

Discontinued on: Jan 23, 2021



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPG	
Product Destination	For Ø 22 mm control and signalling units	
Number Of Cut-Out	Undrilled	
Colour Of Base Of Enclosure	Grey RAL 7032)	
Colour Of Cover	Grey RAL 7032)	
Control Station Type	Metal	
Material	Die cast zinc	
Sale Per Indivisible Quantity	1	
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010	
Resistance To Chemical Agents	Special treatment can be obtained on request	

Complementary

Number Of Vertical Rows	0
Number Of Horizontal Rows	0
Cut-Out Dimensions	Ø 22 mm
Cable Entry	cable gland 1 x cable gland
Thread Type	3/4 NPT
Cad Overall Width	3.15 in (80 mm)
Cad Overall Height	3.15 in (80 mm)
Cad Overall Depth	2.03 in (51.5 mm)
Net Weight	1.01 lb(US) (0.460 kg)
Compatibility Code	XAPG

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030
Ik Degree Of Protection	IK07 EN/IEC 62262

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389118381933
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	16.23 oz (460.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov