Product data sheet

Specification





empty control station - XAP-J - metal - without opening

XAPJ14

! Discontinued on: Oct 20, 2020

! Discontinued

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	XAPJ					
Product Front Plate Size	80 x 80 mm					
Usable Depth	2.93 in (74.5 mm)					
Number Of Cut-Out	Undrilled					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Yellow					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland 0.55 in (14 mm)					
Product Mounting	Flush mounting					
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K					

Complementary

Net Weight 1.34 lb(US) (0.61 kg)

Environment

Protective Treatment	TC				
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)				
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)				
Electrical Shock Protection Class	Class I IEC 60536				

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)				
Discount Schedule	CS2				
Gtin	3389110663693				
Returnability	No				

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	3.54 in (9 cm)
Package 1 Length	3.62 in (9.2 cm)
Package 1 Weight	25.64 oz (727 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	End of Life Information						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.

а		b		С		G		Н		Р	
mm	in.	mm	in.								
80	3.15	80	3.15	77	3.03	50	1.97	65	2.56	74.5	2.93