Product data sheet

Specifications





Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, 2 cut-outs, Ø22, with ISO cable entries, 80 x 130 x 51.5 mm

XAPM2202H29

- () Discontinued on: Jun 30, 2022
- (!) End-of-service on: Jul 28, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	ХАРМ					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	80 x 130 mm					
Usable Depth	1.93 in (49 mm)					
Number Of Cut-Out	2 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland 0.79 in (20 mm) 1 hole without blanking plug for ISO 429248 cable gland 0.79 in (20 mm)					
Device Mounting	Flush					
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K					

Complementary

Number Of Vertical Rows	1						
Net Weight	1.34 lb(US) (0.61 kg)						
Environment							
Protective Treatment	TC						
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)						
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)						
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030						

Ordering and shipping details

Category

US10CS222466

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Discount Schedule	0CS2			
Gtin	3389118115545			
Returnability	No			

Packing Units

Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	3.46 in (8.8 cm)				
Package 1 Width	3.74 in (9.5 cm)				
Package 1 Length	6.14 in (15.6 cm)				
Package 1 Weight	25.33 oz (718 g)				

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity

- (3) $2 \times \emptyset 5.6 \text{ mm}/0.22 \text{ in. holes, depth } 20 \text{ mm}/0.78 \text{ in.}$
- P Usable depth

а		b		с		G		Н		P	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	130	5.12	51.5	2.03	50	1.97	115	4.53	49	1.93

Refer to the product characteristics to get the number of cut-outs. **Cut-out interaxis dimensions**



b1 Vertical interaxis: 40 mm/1.57 in.