
Product data sheet

Specifications





Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, 6 cut-outs, Ø22, 80 x 220 x 77 mm

XAPM4506

Uiscontinued on: Aug 30, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	ХАРМ					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	80 x 220 mm					
Usable Depth	2.93 in (74.5 mm)					
Number Of Cut-Out	6 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole without blanking plug for cable gland 0.71 in (18 mm)					
Device Mounting	Flush					
Ip Degree Of Protection	IP65 IEC 60529					

Complementary

Number Of Vertical Rows	1
Net Weight	3.04 lb(US) (1.38 kg)

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	US10CS222475			
Discount Schedule	0CS2			
Gtin	3389110312973			
Returnability	No			

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of	Origin	
------------	--------	--

MA

Dooking	Linita
Packing	Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.46 in (8.8 cm)
Package 1 Width	5.12 in (13 cm)
Package 1 Length	9.17 in (23.3 cm)
Package 1 Weight	3.43 lb(US) (1.558 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

Product data sheet

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity
- (3) 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.

P Usable depth

a b		с		G		Н		Р			
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	220	6.89	77	3.03	50	1.97	205	8.07	74.5	2.93

Refer to the product characteristics to get the number of cut-outs. **Cut-out interaxis dimensions**



b1 Vertical interaxis: 30 mm/1.18 in.