Product data sheet

Specifications





Harmony XAP, XB2 SL, Empty control station, aluminium, blue, undrilled, 85 x 310 x 77 mm

XAPM54

- Discontinued on: Jun 30, 2022
- ! End-of-service on: Jul 28, 2022

Main

Range Of Product	Harmony XAP			
Product Or Component Type	Die-cast empty control station			
Device Short Name	XAPM			
Product Front Plate Size	85 x 310 mm			
Usable Depth	2.93 in (74.5 mm)			
Number Of Cut-Out	Undrilled			
Colour Of Base Of Enclosure	Blue			
Colour Of Cover	Blue			
Material	Aluminium alloy			
Cable Entry	1 hole without blanking plug for cable gland 0.94 in (24 mm)			
Product Mounting	Flush mounting			
Ip Degree Of Protection	IP65 IEC 60529			

Complementary

Net Weight 1.87 lb(US) (0.85 kg)

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I IEC 60536

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)				
Discount Schedule	CS2				
Gtin	3389110312737				
Returnability	No				
Country Of Origin	FR				

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.92 in (12.5 cm)
Package 1 Width	3.54 in (9 cm)
Package 1 Length	12.40 in (31.5 cm)
Package 1 Weight	34.25 oz (971 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 24 mm/0.94 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.

а		b		С		G		Н		Р		
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
	80	3.15	310	12.20	77	3.03	50	1.97	295	11.61	74.5	2.93