

Product data sheet

Characteristics

XB6EDF1J2P

rectangle white illumin pushbutton Ø16-flush
pushtorelease 12 VDCpolarised 2CO

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 18.00 USD

XB6EDF1J2P has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Range of product	Harmony XB6E
Product or component type	Illuminated monolithic push-button
Device short name	XB6E
Bezel material	Plastic
Mounting diameter	0.63 in (16 mm)
Sale per indivisible quantity	5
Shape of signaling unit head	Rectangular
Type of operator	Latching
Operator profile	White flush
Contacts type and composition	2 C/O
Contact operation	Snap action
Connections - terminals	Faston connectors: 2.8 x 0.5 mm Soldered connectors
Contacts material	Gold-flashed silver
Light source	Integral LED
[Us] rated supply voltage	12 V DC polarised

Complementary

Height	0.71 in (18 mm)
Width	0.94 in (24 mm)
Depth	1.57 in (40 mm)
Terminals description ISO n°1	(23-24-21-22)OF (13-14-11-12)OF
Product weight	0.01 lb(US) (0.006 kg)
Overvoltage category	II conforming to IEC 60536
Operating position	Any position
Marking	CE
Operating force	1.3 N (C/O changing electrical state)
Mechanical durability	250000 cycles
Short-circuit protection	3 A by gG cartridge fuse

[Ith] conventional free air thermal current	3 A
[Ui] rated insulation voltage	250 V (degree of pollution: 2) conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-1
Electrical durability	50000 cycles DC-12, 1 A - 30 V conforming to IEC 60947-5-1 appendix C 50000 cycles AC-12, 0.5 A - 125 V conforming to IEC 60947-5-1 appendix C 50000 cycles AC-12, 0.5 A - 250 V conforming to IEC 60947-5-1 appendix C
Electrical reliability	$\Lambda = 10\exp(-8)$ at 5 V and 1 mA with confidence level of 90 % conforming to IEC 60947-5-4
Signalling type	Steady
Current consumption	20 mA
Service life	50000 h

Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	14...131 °F (-10...55 °C)
IP degree of protection	IP65 conforming to IEC 60529
Standards	UL 508 IEC 60947-1 JIS C 852 CSA C22.2 No 14 JIS C 4520 IEC 60947-5-1
Product certifications	CCC cURus
Vibration resistance	1 mm (5...55 Hz) conforming to IEC 60068-2-6 9 gn (5...55 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27
Electromagnetic compatibility	Electrostatic discharge immunity test 8 kV - test level conforming to IEC 61000-4-2

Ordering and shipping details

Category	22459 - PUSHBUTTONS, 16MM
Discount Schedule	CS2
GTIN	003389110631678
Nbr. of units in pkg.	5
Package weight(Lbs)	0.13
Returnability	N
Country of origin	CN

Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Pushbutton

Rectangular Head



- (1) Anti-rotation plate (thickness: 0.6 mm / 0.02 in.)
- (2) Seal (thickness: 0.5 mm / 0.01 in.)
- e panel thickness: 0.5 mm (0.01 in.) ≤ e ≤ 6 mm (0.24 in.)

Panel Cut-Out and Mounting

Rectangular Head

