

XMLE600U1C43 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range of product	OsiSense XM
Product or component type	Electronic pressure sensors
Pressure sensor type	Electronic pressure sensor
Pressure sensor size	8702.26 psi (600 bar)
Pressure sensor name	XMLE
Controlled fluid	Fresh water (32...176 °F (0...80 °C)) Air (5...176 °F (-15...80 °C)) Corrosive fluid (5...176 °F (-15...80 °C)) Hydraulic oil (5...176 °F (-15...80 °C))
Fluid connection type	1/4" - 18 NPT (male)
Type of output signal	Discrete
Discrete output type	Solid state PNP, 1 NC
Electrical connection	Male connector EN 175301-803-A (ex DIN43650)
Adjustable range of switching point on rising pressure	609.16...8702.26 psi (42...600 bar)
Adjustable range of switching point on falling pressure	435.11...8528.22 psi (30...588 bar)
[Us] rated supply voltage	24 V DC, voltage limits: 11...33 V
Diameter	1.57 in (40 mm)

Complementary

Enclosure material	Anodised aluminium
Type of installation	Control circuit
Operating position	Any position
Materials in contact with fluid	Stainless steel type AISI 303
Pressure switch type of operation	Regulation between 2 thresholds
Possible differential minimum at low setting	174.05 psi (12 bar)
Possible differential maximum at high setting	174.05 psi (12 bar)
Maximum permissible accidental pressure	17404.53 psi (1200 bar)
Maximum permissible pressure - per cycle	8702.26 psi (600 bar)

Destruction pressure	26106.79 psi (1800 bar)
Drift of the sensitivity	+/- 0.015 % of measuring range/°C
Drift of the zero point	+/- 0.03 % of measuring range/°C
Protection type	Overload protection Reverse polarity Short-circuit
Scale type	Adjustable differential
Local display	Without
Mechanical durability	>= 10000000 cycles
Measurement accuracy	+/- 0.3 % of the measuring range
Product weight	0.6 lb(US) (0.27 kg)

Environment

IP degree of protection	IP65
Vibration resistance	35 gn (f = 60...2000 Hz) 5 gn (f = 25...200 Hz)
Protective treatment	TC
Shock resistance	50 gn
Standards	CE EN 50081 EN 50082
Product certifications	CSA UL
Ambient air temperature for operation	5...176 °F (-15...80 °C)

Ordering and shipping details

Category	21551 - XMLE,XMLF,XMLG PRESSURE SENSORS
Discount Schedule	DS2
GTIN	003389110758788
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5999999999999998
Returnability	N
Country of origin	CH


Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions



Ø : 1/2 NPT


Dimensions in mm

a
75


Dimensions in in.

a
2.95

Wiring Diagram



Operating Curves



- 1 : Maximum differential
- 2 : Minimum differential
- (y) Rising pressure
- (x) Falling pressure